

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

V7-6B19D8-057

CW-C6001

X97774-V7

REPLACES

RELEASE NO. PR-20758

CATALOG LISTING

V7-6B19D8-057

M

ISSUE
2

CHECK

REVISIONS

A	0085964
SBH	30JAN12

CHECK

30JAN12



CMH

CHECK

93

G R T
DRAWN


24 SEP



ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	NONE	DO NOT SCALE PRINT
OPERATING FORCE — — 55 GRAMS MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — 3 GRAMS MIN				
DIFFERENTIAL TRAVEL — — — .100 MAX	L156 11A 1/3HP 125, 250 OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L"	ONE PLACE (.0)	±.030	
OVERTRAVEL — — — — — .145 MIN		TWO PLACE (.00)	±.015	
RELEASE TRAVEL — — — — — .035 MIN		THREE PLACE (.000)	±.005	
		ANGLES	±	
		WEIGHT		

