

SPECIFICATION




■ Features :

- 2:1 wide input range
- 4:1 wide input range(option)
- 1000VDC I/O isolation
- 3000VDC I/O isolation(option)
- Built-in EMI filter
- Protections: Short circuit / Overload
- Cooling by free air convection
- Six-sided shield metal case
- 100% burn-in test
- Low cost / High reliability
- Approvals: FCC / CE
- · 2 years warranty

FC III CE

| ORDER NO. | | SKE10A- 05 | SKE10B- 05 | SKE10C- 05 | SKE10A- 12 | SKE10B- 12 | SKE10C- 12 | SKE10A- 15 | SKE10B- 15 | SKE10C- 15 | SKE10A- 24 | SKE10B- 24 | SKE10C- 24 |
|-------------------------|------------------------------|---|--|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|
| ОИТРИТ | DC VOLTAGE | 5V | | | 12V | | | 15V | | | 24V | | |
| | CURRENT RANGE | 200 ~ 2000mA | | | 84 ~ 840mA | | | 66.6 ~ 666mA | | | 42 ~ 420mA | | |
| | RATED POWER | 10W | | | | | | | | | ' | | |
| | RIPPLE & NOISE (max.) Note.2 | 50mVp-p | | | 60mVp-p | | | 60mVp-p | | | 80mVp-p | | |
| | LINE REGULATION Note.3 | ±0.3% | | | | | | | | | | | |
| | LOAD REGULATION Note.4 | ±0.5% | | | | | | | | | | | |
| | VOLTAGE ACCURACY | ±2.0% | ±2.0% | | | | | | | | | | |
| | SWITCHING FREQUENCY | 200KHz min. | | | | | | | | | | | |
| INPUT | VOLTAGE RANGE | A: 9 ~ 18VDC B: 18 ~ 36VDC C: 36 ~ 72VDC | | | | | | | | | | | |
| | EFFICIENCY (Typ.) | 78% | 79% | 80% | 79% | 81% | 81% | 80% | 82% | 82% | 81% | 82% | 83% |
| | DC CURRENT | Full load A: 1100mA B: 530mA C: 270mA | | | | | | | | | | | |
| | | No load A: 28mA B: 16mA C: 8mA | | | | | | | | | | | |
| | FILTER | Pi network | | | | | | | | | | | |
| | PROTECTION | Fuse recommended | | | | | | | | | | | |
| PROTECTION (Note. 5) | OVER CURRENT | 160% ~ 250% rated output power | | | | | | | | | | | |
| | OVER CURRENT | Protection type: Hiccup mode, recovers automatically after fault condition is removed | | | | | | | | | | | |
| | SHORT CIRCUIT | All output equipped with short circuit | | | | | | | | | | | |
| | SHOKT CIRCUIT | Protection type: Hiccup mode, recovers automatically after fault condition is removed | | | | | | | | | | | |
| ENVIRONMENT | WORKING TEMP. | -25 ~ +71°C (Refer to "Derating Curve") | | | | | | | | | | | |
| | WORKING HUMIDITY | 20% ~ 90% RH non-condensing | | | | | | | | | | | |
| | STORAGE TEMP., HUMIDITY | -25 ~ +105°C, 10 ~ 95% RH | | | | | | | | | | | |
| | TEMP. COEFFICIENT | ±0.03% / °C (0 ~ 50°C) | | | | | | | | | | | |
| | VIBRATION | 10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes | | | | | | | | | | | |
| SAFETY & EMC | SAFETY STANDARDS | EAC TP TC 004 approved | | | | | | | | | | | |
| | WITHSTAND VOLTAGE | I/P-O/P:1KVDC | | | | | | | | | | | |
| | ISOLATION RESISTANCE | I/P-O/P: 100M Ohms / 500VDC / 25°C / 70% RH | | | | | | | | | | | |
| | EMC EMISSION | Compliance to EN55032 Class A, FCC part 15 Class A, EAC TP TC 020 | | | | | | | | | | | |
| | EMC IMMUNITY | Complian | Compliance to EN61000-4-2,3,4,5,6,8, light industry level, criteria A, EAC TP TC 020 | | | | | | | | | | |
| OTHERS | MTBF | 500Khrs min. MIL-HDBK-217F(25°C) | | | | | | | | | | | |
| | DIMENSION | 50.8*25.4*11.2mm or 2"*1"*0.44" inch (L*W*H) | | | | | | | | | | | |
| | WEIGHT | 32g | | | | | | | | | | | |


■ Mechanical Specification



■ Pin Configuration

| Pinno. | Output | | | | | |
|-----------|--------|--|--|--|--|--|
| 1 111110. | Single | | | | | |
| 1 | +Vin | | | | | |
| 2 | -Vin | | | | | |
| 3 | +Vout | | | | | |
| 4 | No Pin | | | | | |
| 5 | -Vout | | | | | |

■ Derating Curve



NOTE

- 1.All parameters are specified at normal input, rated load, 25°C 70% RH ambient.
 2.Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uf & 47uf capacitor.
 3.Line regulation is measured from low line to high line at rated load.
 4.Load regulation is measured from 10% to 100% rated load.

- 5.Please prevent the converter from operating in overload or short circuit condition for more than 30 seconds.