



NBNC75BIJ9

The rearTWIST HD BNC cable connector offers a true 75 Ω design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cables:

Belden 1506A, Belden 4505P, CommScope 2065V, Cordial CVM 08-32 HD-FLEX

Crimp size:

Pin: 1.6 mm (square)

Shield: 5.41 mm (hex)

Features & Benefits

- "rearTWIST Principle" locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- True 75 Ω design meets the stringent HDTV / DVD requirements
- Snug-fit center pin insert provides tactile feedback
- Excellent cable protection and retention
- Accessories include color coded boots in 10 standard colors, crimp tool and dies
- Ideal for recessed bulkheads where access to the "head" of the connector might be an issue. These connectors turn from the back and not the front.
- Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!
- Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- Precise Swiss machined brass parts for outstanding durability

Technical Information

Product	
Title	NBNC75BIJ9
Connection Type	BNC 75 Ω
Gender	male

Electrical	
Contact resistance	≤ 3 m Ω (inner)
Contact resistance	≤ 2 m Ω (outer)
Dielectric strength	1,5 kVdc
Impedance	75 Ω
Insulation resistance	> 5 G Ω
Rated voltage	< 50 V
VSWR	$\leq 1.050 / > 32$ dB up to 1 GHz $\leq 1.065 / > 30$ dB up to 2 GHz $\leq 1.100 / > 26$ dB up to 3 Ghz

Mechanical	
Cable O.D.	5.3 mm
Cable retention	> 30 N (Center)
Crimp size	5,41 Hex crimp (shield) acc. IEC 60803 (die designation D)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material	
Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental	
Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2