



NC4FAV-0

4 pole female XLR receptacle, grounding: separate ground contact to mating connector shell and front panel, vertical PCB mount, Retention spring instead of latch, color coding possible

The 'State of the Art' receptacle. Round plastic body XLR PCB mount panel connector. These have the smallest size and highest packing density (23 mm between centres). New designed fork type contacts with hard gold plating and polished contact areas.

Features & Benefits

- Smallest XLR receptacles, highest packing density
- Fork type female contact
- Housing flammability UL94HB
- Plastic housing, steel retention spring
- Polished contact areas and hard gold plating

Technical Information

Product	
Title	NC4FAV-0
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	≤ 7 pF
Contact resistance	≤ 6 m Ω
Dielectric strength	1,5 kVdc
Insulation resistance	> 10 G Ω (initial)
Rated current per contact	6 A
Rated voltage	< 50 V
Grounding Options	separate ground contact to mating connector shell and front panel

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Locking force	> 20 separating force N
Wiresize	
Wiring	vertical PCB mount
Locking device	Retention spring
Mounting direction	Rear mounting
Chassis shape	A
Mounting	A-Screw

Material	
Contacts	Bronze (CuSn6)
Locking element	Steel Ck67
Shell	Polyamide (PA 6.6 30 % GR)

Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C