



NC4MAH

4 pole male XLR receptacle, grounding: separate ground contact to mating connector shell and front panel, horizontal PCB mount, color coding possible

The 'State of the Art' receptacle. Round plastic body XLR PCB mount panel connector. These have the smallest size and highest packing density (23 mm between centres). New designed fork type contacts with hard gold plating and polished contact areas.

Features & Benefits

- Smallest XLR receptacles, highest packing density
- Polished contact areas and hard gold plating
- Plastic housing, steel latch lock
- Housing flammability UL94HB

Technical Information

Product	
Title	NC4MAH
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	≤ 7 pF
Contact resistance	≤ 6 m Ω
Dielectric strength	1,5 kVdc
Insulation resistance	> 10 G Ω (initial)
Rated current per contact	6 A
Rated voltage	< 50 V
Grounding Options	Separate ground contact connected to mating connector shell and front panel, no connection to Pin 1

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	A
Mounting	A-Screw

Material	
Contacts	Brass (CuZn35Pb2)
Shell	Polyamide (PA 6.6 30 % GR)

Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C