



NC7MXX-BAG

7 pole male cable connector with black metal housing and silver contacts.

The next generation of the worldwide accepted standard of XLR cable connectors. The successor of the X series offers several new features which make it more reliable, easier to assemble and improves contact integrity as well cable strain relief.

Features & Benefits

- Male connector with improved locking recess without "window", more stringent housing increases durability
- Boot with polyurethane gland gives high protection to cable bending stresses
- Sleek and ergonomic design - valuable and handy
- Internal thread on shell is well protected against any damage
- Improved chuck type strain relief provides higher pull-out force and makes assembly easier and faster
- Colored rings and boots available for coding or identification
- Rugged zinc diecast shell, longlasting and dependable
- Branded with unique hologram - guarantees genuine and authentic Neutrik product

Technical Information

Product	
Title	NC7MXX-BAG
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	≤ 9 pF
Contact resistance	≤ 3 m Ω
Dielectric strength	1,5 kVdc
Insulation resistance	> 10 G Ω (initial)
Rated current per contact	5 A
Rated voltage	< 50 V

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	max. 1.0 mm ²
Wiresize	max. 18 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Zinc diecast (ZnAl4Cu1)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium
Strain relief	Polyacetal (POM)

Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C