


## 5-1393812-2 Product Details



### 5-1393812-2

TE Part Number: 5-1393812-2

✓ Active

➤ [Add to Part List](#)

## Communications/Signal PC Board Relays

✓ [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

### Product Highlights:

- V23054/Cradle Relay S Series
- DC Actuating System
- Input Voltage = 24 VDC
- Contact Arrangement = 6 Form A, 6PST-NO, 6 N/O
- Contact Current Rating = 2 Amps.

[View all Features](#) | [Find Similar Products](#)

## Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

## Documentation & Additional Information

### Product Drawings:

- None Available

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- [Cradle S Relay Datasheet](#) (PDF, English)

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Termination Type = Solder/Plug-In Terminals

### Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 24
- Contact Current Rating (Amps.) = 2
- [Coil Resistance \( \$\Omega\$ \)](#) = 630
- Coil Power, Nominal (mW) = 1000
- Dielectric Between Coil and Contacts (V rms) = 500

### Body Related Features:

- [Series](#) = V23054/Cradle Relay S
- Polarized = No

### Contact Related Features:

- Mounting Options = Socket
- Enclosure = Dust Protected
- [FCC Part 68 Isolation](#) = No
- Approved Standards = None
- Contact Material = Silver, Gold Overlay
- Approx. Dimensions (L x W x H) (mm [in]) = 30.00 x 19.00 x 30.00 [1.181 x .748 x 1.181]
- Compatible Socket = With
- Contact Type = Single
- Pin Configuration = Industry Standard

### Configuration Related Features:

- [Contact Arrangement](#) = 6 Form A, 6PST-NO, 6 N/O
- [Coil Magnetic System](#) = Non Polarized, Monostable
- Coil Suppression Diode = Without

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

### Other:

- Brand = Axicom