

Features


- Monitors AC Single Phase and DC Voltages
- Wide Range of User-Adjustable Pick-Up and Drop-Out Settings
- LED Indicates Output Relay Status
- Compact 8-Pin Octal Plug-In Case



OPERATION

Voltage Monitor Relays provide protection to equipment where an over or under voltage condition is potentially damaging. They monitor either AC single phase (50–400Hz) or DC voltages. No supply (input) voltage is required.

The pick-up voltage setting is user-adjustable from 85–115% of the nominal voltage rating. As standard, the drop-out voltage setting is fixed at 3% below the pick-up voltage setting. The relay is energized when the monitored voltage is above the pick-up setting. The relay de-energizes when the monitored voltage is below the drop-out setting.



AC OPERATED						
NTE Type No.	Nom. Voltage	Contact Arr.	Pick-up Voltage Range	Drop-out Voltage Range*	Max. Contact Cur. @ 30VDC or 240VAC	Diag No.
R67-11A10-24	24VAC	DPDT	21–27V	20–26V	10A	D61
R67-11A10-120	120VAC	DPDT	102–138V	99–134V	10A	D61
DC OPERATED						
R67-11D10-24	24VDC	DPDT	21–27V	20–26V	10A	D61



* Fixed at 3% below the pick-up setting.

ACCESSORIES		
MOUNTING STYLES	DESCRIPTION	NTE TYPE NO.
SURFACE MOUNT	8-PIN OCTAL	R95-101
PANEL MOUNT	8-PIN OCTAL	R95-118
DIN RAIL MOUNT	8-PIN OCTAL	R95-113


R67 Series

Voltage Monitoring, DPDT, 10 Amp, AC & DC Relay.

D61



DPDT, 2 Form "C"



Electrical Specifications

Contact

Rating: 10 Amps resistive at 240VAC, 1/2 HP at 240VAC,

10 Amps resistive at 30VDC

Life: 500,000 operations at full load

Mechanical Life: 7,000,000 operations at no load

Operational Characteristics

Voltage Settings: .. **Pick-up:** Adjustable from 85–115% of nom

Drop-out: Fixed at 3% below pick-up setting

Setting Accuracy: +0%, -5% min; +5%, -0% max

Timing Values: **Operate Time:** 50 mS

Release Time: 50 mS

Power Required: 3VA

Protection

Transient: 10,000V for 20μs

Indicator LED: Red LED on when relay is energized

Reset: Automatic

Environmental Characteristics

Operating: -28°C to +65°C

Note: UL Recognition Pending.