

MOS FET Relays

G3VM-354C/C1/F/F1

Analog-switching MOS FET Relays with DPST-NC Contact.

General-purpose Models Added.


- Switches minute analog signals.
- Switching AC and DC.
- General-purpose models (models with high ON resistance) added to the series.

RoHS compliant

⚠ Refer to "Common Precautions".

Application Examples

- Electronic automatic exchange systems
- Security systems
- Datacom (modem) systems
- FA systems
- Measurement devices



Note: The actual product is marked differently from the image shown here.


List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per stick	Number per tape
DPST-NC	PCB terminals	350 VAC	G3VM-354C	50	---
			G3VM-354C1		
			G3VM-354F		
			G3VM-354F1		
	Surface-mounting terminals		G3VM-354F(TR)	---	1,500
			G3VM-354F1(TR)		

Dimensions


Note: All units are in millimeters unless otherwise indicated.

G3VM-354C/C1



Note: The actual product is marked differently from the image shown here.


G3VM-354F/F1




Note: The actual product is marked differently from the image shown here.

Terminal Arrangement/Internal Connections (Top View)

G3VM-354C/C1




G3VM-354F/F1




PCB Dimensions (Bottom View)

G3VM-354C/C1



Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-354F/F1



Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Rating	Unit	Measurement Conditions	
Input	LED forward current	I _F	50	mA	
	Repetitive peak LED forward current	I _{FP}	1	A	100 μs pulses, 100 pps
	LED forward current reduction rate	Δ I _F /°C	-0.5	mA/°C	Ta ≥ 25°C
	LED reverse voltage	V _R	5	V	
	Connection temperature	T _j	125	°C	
Output	Output dielectric strength	V _{OFF}	350	V	
	Continuous load current	I _O	150 (100)	mA	
	ON current reduction rate	Δ I _{ON} /°C	-1.5 (-1)	mA/°C	Ta ≥ 25°C
	Connection temperature	T _j	125	°C	
Dielectric strength between input and output (See note 1.)		V _{I-O}	2,500	Vrms	AC for 1 min
Operating temperature		T _a	-40 to +85	°C	With no icing or condensation
Storage temperature		T _{stg}	-55 to +125	°C	With no icing or condensation
Soldering temperature (10 s)		---	260	°C	10 s

Values in parentheses are for the G3VM-354C1/F1.


Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions	
Input	LED forward voltage	V _F	1.0	1.15	1.3	V	I _F = 10 mA
	Reverse current	I _R	---	---	10	μA	V _R = 5 V
	Capacity between terminals	C _T	---	30	---	pF	V = 0, f = 1 MHz
	Trigger LED forward current	I _{FT}	---	1	3	mA	I _{OFF} = 10 μA
Output	Maximum resistance with output ON	R _{ON}	---	15 (30)	25 (50)	Ω	I _O = 150 mA
	Current leakage when the relay is open	I _{LEAK}	---	---	1.0	μA	I _F = 5 mA, V _{OFF} = 350 V
Capacity between I/O terminals		C _{I-O}	---	0.8	---	pF	f = 1 MHz, V _S = 0 V
Insulation resistance		R _{I-O}	1,000	---	---	MΩ	V _{I-O} = 500 VDC, RoH ≤ 60%
Turn-ON time		t _{ON}	---	0.1 (0.25)	1.0 (0.5)	ms	I _F = 5 mA, R _L = 200 Ω, V _{DD} = 20 V (See note 2.)
Turn-OFF time		t _{OFF}	---	1.0 (0.5)	3.0 (1)	ms	

Values in parentheses are for the G3VM-354C1/F1.

Note: 2. Turn-ON and Turn-OFF Times



Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Output dielectric strength	V _{DD}	---	---	280	V
Operating LED forward current	I _F	5	---	25	mA
Continuous load current	I _O	---	---	150 (100)	mA
Operating temperature	T _a	-20	---	65	°C

Values in parentheses are for the G3VM-354C1/F1.

Engineering Data

Load Current vs. Ambient Temperature

G3VM-354C(F)
G3VM-354C1/F1



Safety Precautions

Refer to "Common Precautions" for all G3VM models.