

Zack Marker strip, flat - ZBF 12:UNBEDRUCKT - 0809735

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 12 mm, Lettering field: 5.15 x 12.15 mm

The illustration shows the 15 mm wide version

Product Features

- Can be labeled with CMS computer marking system or by hand using B-STIFT
- Sealing caps with external or inner thread
- Printed or unprinted marking labels
- Consists of five individual labels with 17.5 mm pitch
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- Flat zack marker strips

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	0.66 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	12 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA

Zack Marker strip, flat - ZBF 12:UNBEDRUCKT - 0809735

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	5
Marking mounting type	Snap into flat marker groove

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410