

## VTF



Powertrain Systems



Chassis Systems



Safety



Security



Body



Driver Information



Convenience

### Description

#### Features

- Combination turn signal and hazard warning signal flasher<sup>1)</sup>
- Lamp outage sensing. Double flash rate
- Meets all applicable U.S.A. safety standards
- Stable electronic timing
- VKP relay with PdCu contact for output
- Fits ISO 7588 socket
- Wide operating voltage and temperature range

#### Typical applications

Flasher and turn signals

1) Caution:

Three lamp combination flashers with three terminals do not meet U.S. Federal motor vehicle safety requirements when lamp outage occurs during hazard mode operation. For more information consult factory.

Please contact Tyco Electronics for relay application support.



Car Industry



Truck Industry



Other Industry

VTF\_3d01

#### Design

Dustproof, plastic enclosure

#### Weight

Approx. 1.3 oz. (37 g)

#### Nominal voltage

12 V;  
other nominal voltages available on request

#### Terminals

0.250 " (6.35 mm) quick connect terminals

#### Accessories

Connectors see page 192

#### Conditions

All parametric, environmental and endurance tests are performed according to EIA Standard RS-407-A at standard test conditions unless otherwise noted:



23 °C ambient temperature,  
20-50% RH, 29.5 ± 1.0" Hg  
998.9 ±33.9 hPa).

Please also refer to the Application Recommendations in this catalog for general precautions.

**OBSOLETE**  
**NOT the LATEST**  
**REVISION**

#### Disclaimer

All technical performance data apply to the relay as such, specific conditions of the individual application are not considered. Please always check the suitability of the relay for your intended purpose. We do not assume any responsibility or liability for not complying herewith. We recommend to complete our questionnaire and to request our technical service. Any responsibility for the application of the product remains with the customer only. All specifications are subject to change without notification. All rights of Tyco are reserved.

**VTF****Dimensional drawing****View of the terminals (Bottom view)**

## VTF


### Contact data: load requirements at 12.8 V

Loads		European		U.S.A.		
		2 Lamp system	3 Lamp system	2 Lamp system	3 Lamp system	5 Lamp system
Turn signal mode:	Rated loads	2 x 21 W + 1 x 5 W + 1 x 1.2 W	3 x 21 W + 1 x 5 W + 1 x 1.2 W	2 x 27 W + 1 x 3.5 W + 1 x 1.3 W	3 x 27 W + 1 x 3.5 W + 1 x 1.3 W	5 x 27 W + 1 x 3.5 W + 1 x 1.3 W
	Outage loads	1 x 21 W + 1 x 5 W + 1 x 1.2 W	2 x 21 W + 1 x 5 W + 1 x 1.2 W	1 x 27 W + 1 x 3.5 W + 1 x 1.3 W	2 x 27 W + 1 x 3.5 W + 1 x 1.3 W	Not applicable
	Rated loads	4 x 21 W + 2 x 5 W + 2 x 1.2 W	6 x 21 W + 2 x 5 W + 2 x 1.2 W	4 x 27 W + 2 x 3.5 W + 2 x 1.3 W	6 x 27 W + 2 x 3.5 W + 2 x 1.3 W	10 x 27 W + 2 x 3.5 W + 2 x 1.3 W
	Outage loads					


### Flash rate and duty cycle data

Turn signal mode:	Normal signal		
	FPM	70 – 100	
	Duty cycle	35 – 55%	
Outage signal			
% Increase		80 – 200	
Duty cycle		35 – 55 %	
Hazard mode:	Normal signal		
	FPM	70 – 110	
	Duty cycle	35 – 55 %	

### Electrical contact life vs. load power



### Pin assignment



**VTF****Coil data**

Available for nominal voltages	12 V (other coils on request)
Operating voltage range	9 – 16 V
Device voltage drop	< 0.4 V at rated turn signal load < 0.45 V at rated hazard signal load
Initial turn-on time	≤ 50 ms
Start time	< 1 s per FMVSS 108
Sound pressure level	Min. 72 dBA at 1.0 m <sup>1</sup> )
Maximum ambient temperature range <sup>2</sup> )	– 40 to + 85 °C

<sup>1)</sup> The actual sound pressure is highly dependend on mounting method used.

<sup>2)</sup> See also operating voltage diagram

N.B.

A low resistive device in parallel to the relay coil slows the armature movement down and reduces the lifetime caused by increased erosion and/or higher risk of contact tack welding.

**Mechanical data**

Cover retention				
Axial force	150 N (33.7 lbs)			
Pull force	220 N (50 lbs)			
Push force	220 N (50 lbs)			
Terminals				
Pull force	100 N (22.5 lbs)			
Push force	100 N (22.5 lbs)			
Enclosures				
Dust cover	Protects relay from dust. For use in passenger compartment or enclosures			

**Operating conditions**

Temperature range, storage		Refer to <i>Storage</i> in the "Glossary"				
Test	Relevant standard	Testing as per		Dimension	Comments	
Vibration resistance	1.27 mm double amplitude		10 - 40 Hz		No change in the switching state > 1 ms	
	5 g contant		40 - 70 Hz			
	0.5 mm double amplitude		70 - 100 Hz			
	10 g constant		100 - 500 Hz			
Shock resistance	Half sine wave pulse			10 ms	No change in the switching state > 1 ms	
				20 g		
Drop test	Capable of meeting specifications after 1.0 m (3.28 foot) drop onto concrete					
Flammability	UL94-HB or better (meets FMVSS 302)					

**Ordering information**

Part numbers (see table below for coil data)		Meets the safety standard of		Flasher type		Turn signal mode			Max. number of lamps		Lamp outage sensing			
Relay part number	Tyco order number	U.S.A.	European signal	Turn	Turn/Hazard warning	Hazard	2 Lamp system	3 Lamp system	5 Lamp system	Hazard	Normal	Special	Yes	No
VTF-11F21	Not established	X		X			X				3	5	X	
VTF-11F31	5-1419084-9	X		X				X			4	7	X	
VTF-12F21	1393317-3	X			X		X				4	6		X
VTF-13F21	Not established	X				X	X				4	6		X
VTF-21F21	Not established		X	X			X				3		X	
VTF-21F31	Not established		X	X				X			4		X	
VTF-22F21	6-1419084-0		X		X		X				4	6		X
VTF-22F31	6-1419084-1		X		X			X			6		X	
VTF-14F11	1-1393317-3	X			X				X	10				X

**Standard delivery pack** (orders in multiples of delivery pack)

VTF: 400 pieces