

MDR-138-8 Product Details



MDR-138-8 (1-1393139-2)

TE Part Number: 1-1393139-2

 [Active](#)

 [Add to Part List](#)

Rotary Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Contact Arrangement = 8 Form C, 8PDT, 8 C/O
- DC Actuating System
- Input Voltage = 125 VDC
- Coil Current = .082 Amps.
- Coil Resistance = 1520 Ω

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Dimensional Drawing](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Comment = Small

Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 125
- Coil Current (Amps.) = 0.082
- Coil Resistance (Ω) = 1520
- Coil Power, Nominal (W) = 10.30
- Breakdown Volts RMS (V) = 2375

Termination Related Features:

- Base Dimensions (mm [in]) = 66.68 x 66.68 [2.625 x 2.625]
- Height (mm [in]) = 89.70 [3.530]

Configuration Related Features:

- [Contact Arrangement](#) = 8 Form C, 8PDT, 8 C/O
- Coil Magnetic System = Non-Latching

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range (°C) = 0 – 65

Other:

- Brand = Potter & Brumfield