



1060 Micro

From small sensitive components to smartphones, protect your gear from the elements in a crushproof, watertight, & dustproof Micro Case from Pelican.

- ***Case is able to be submerged under 1 meter of water for up to 30 minutes in accordance with IP67 testing parameters**
- **Available in clear with color liner or solid**
- **Watertight, crushproof, and dustproof**
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Carabiner
- Easy open latch
- Lifetime Guarantee of Excellence
- Rubber liner for extra protection doubles as o-ring seal
- Stainless steel hardware



DIMENSIONS

Interior (LxWxD)	8.25 x 4.25" x 2.25 (21 x 10.8 x 5.7 cm)
Exterior (LxWxD)	9.88 x 5.59" x 2.63 (25.1 x 14.2 x 6.7 cm)
Lid Depth	0.69" (1.8 cm)
Bottom Depth	1.44" (3.7 cm)
Total Depth	2.13" (5.4 cm)
Int Volume	0.05 ft ³ (0.001 m ³)

MATERIALS

Body	Polycarbonate (PC)
Latch	Xylex
O-Ring	Thermoplastic Rubber
Pins	Stainless Steel
Foam	TL - 426 4 lb. Esther
Purge Body	Polycarbonate (PC)
Purge Vent	Polyester Spun-Bond ePTFE Oleophobic

COLOURS

■ Black	■ OD Green	■ Yellow	■ Tan
■ Seafoam	■ Black - Clear	■ Yellow - Clear	■ Blue - Clear
■ Red - Clear	■ Indigo	■ Bright Green	■ Oxblood

WEIGHT

Weight With Foam	1.03 lbs (0.5 kg)
Weight Empty	1.00 lbs (0.5 kg)
Buoyancy	2.49 lbs (1.1 kg)
Master Pack Weight	7.08 lbs (3.2 kg)

TEMPERATURE

Minimum Temperature	-10°F (-23.3 °C)
----------------------------	------------------

Maximum Temperature 199°F (92.8 °C)

CERTIFICATIONS

IP67

FOAM PROPERTIES

Layer 1 (Lid)	0.13" Pad
Layer 2 (Base)	1.43" Pick N Pluck

OTHER

Minimum Pack	6
Master Pack	6
Military	yes

ACCESSORIES



1061
Replacement Case Liner



1062
Pick N Pluck™ Foam Insert

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 10-03-20