



## 1510LOC

### Protector

#### Laptop Case

Sensitive equipment needs protection, and since 1976 the answer has been the Pelican™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Pelican cases have survived.

Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- Personalized nameplate service available
- **2 in 1 protection: detachable computer sleeve and accessories pouch**
- Maximum airline carry on size\*
- **Strong polyurethane wheels with stainless steel bearings**
- **Watertight, crushproof, and dustproof**
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Comfortable rubber over-molded top and side handles
- Easy open Double Throw latches
- Lifetime Guarantee of Excellence
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Retractable extension handle
- Fits notebook computers up to 14.4" x 11.1" x 1.7" (36.58 x 28.19 x 4.32 cm)
- \* Check with your airline for exact measurement requirements.



## DIMENSIONS

<b>Interior (LxWxD)</b>	19.75 x 11.00" x 7.60 (50.2 x 27.9 x 19.3 cm)
<b>Exterior (LxWxD)</b>	22.00 x 13.81" x 9.00 (55.9 x 35.1 x 22.9 cm)
<b>Lid Depth</b>	1.79" (4.5 cm)
<b>Bottom Depth</b>	5.79" (14.7 cm)
<b>Total Depth</b>	7.58" (19.3 cm)
<b>Int Volume</b>	0.96 ft <sup>3</sup> (0.027 m <sup>3</sup> )
<b>Padlock Hole Diameter</b>	5/16" (8 mm)

## MATERIALS

<b>Body</b>	Polypropylene
<b>Latch</b>	ABS
<b>O-Ring</b>	Polymer
<b>Pins</b>	Stainless Steel
<b>Foam</b>	1.3 lb Polyurethane
<b>Purge Body</b>	ABS
<b>Purge Vent</b>	3 Micron Hydrophobic Non-Woven

## COLOURS

■ Black

## WEIGHT

<b>Weight With Foam</b>	13.60 lbs (6.2 kg)
-------------------------	--------------------

<b>Weight Empty</b>	11.99 lbs (5.4 kg)
<b>Buoyancy</b>	64.15 lbs (29.1 kg)
<b>Master Pack Weight</b>	32.43 lbs (14.7 kg)

---

## TEMPERATURE

<b>Minimum Temperature</b>	-40°F (-40 °C)
<b>Maximum Temperature</b>	210°F (98.9 °C)

---

## CERTIFICATIONS

**IP67**  
**Def Stan 81-41**  
**STANAG 4280**

---

## OTHER

<b>Wheels</b>	2
<b>Extendable Handle</b>	yes
<b>Master Pack</b>	2
<b>Nameplate</b>	yes
<b>Reduced Area</b>	yes
<b>Military</b>	yes

---

## ACCESSORIES



**1513**  
Replacement O-ring



**1506TSA**  
TSA Lock



**1500D**  
Desiccant Silica Gel



**PL2**  
Padlock (2 pack)

---

### Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311  
[sales@pelican.com](mailto:sales@pelican.com) • [www.pelican.com](http://www.pelican.com)

*Document created on 08-15-20*