

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Panel feed-through terminal block, Connection method: Screw connection, Screw connection, Load current: 41 A, Cross section: 0.2 mm² - 6 mm², AWG 24 - 10, Connection direction of the conductor to plug-in direction: 0 °, Width: 8.1 mm, Color: green-yellow

The illustration shows version HDFK 4 in gray



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	4 017918 004255
Weight per Piece (excluding packing)	8.86 g
Custom tariff number	85369010
Country of origin	Greece

Technical data

General

M. observition de	L
Number of levels	1
Number of connections	2
Nominal cross section	4 mm ²
Color	green-yellow
Insulating material	PA
Flammability rating according to UL 94	V0
Rated surge voltage	6 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Nominal current I _N	32 A



Technical data

General

Maximum load current	41 A			
Nominal voltage U _N	400 V (with metal panels of 1 mm 2,5 mm and plastic panels of 1 mm 4 mm. with metal panels over 2.5 mm 4 mm: 250 V)			
	250 V (With metal panels over 2.5 mm 4 mm)			
400 V (With plastic panels of 1 mm 4 mm)				
Open side panel	No			
Number of positions	1			

Dimensions

Width	8.1 mm

Connection data

Connection side	Level 1 ext. 1		
Connection method	Screw connection		
Conductor cross section solid min.	0.2 mm ²		
Conductor cross section solid max.	6 mm²		
Conductor cross section flexible min.	0.2 mm ²		
Conductor cross section flexible max.	4 mm²		
Conductor cross section AWG min.	24		
Conductor cross section AWG max.	10		
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm²		
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm²		
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm²		
Conductor cross section flexible, with ferrule with plastic sleeve max.	4 mm²		
2 conductors with same cross section, solid min.	0.2 mm²		
2 conductors with same cross section, solid max.	1.5 mm ²		
2 conductors with same cross section, stranded min.	0.2 mm²		
2 conductors with same cross section, stranded max.	1.5 mm²		
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm²		
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm²		
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²		
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	ic 2.5 mm ²		
Cross section with insertion bridge, solid max.	4 mm²		
Cross section with insertion bridge, stranded max.	2.5 mm²		
Stripping length	9 mm		
Internal cylindrical gage	A4		



Technical data

Connection data

Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm
Connection side	Level 1 int. 1
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	4 mm²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	10
Internal cylindrical gage	A4

Standards and Regulations

Connection in acc. with standard	CSA	
	IEC / EN	
Flammability rating according to UL 94	V0	

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141134
eCl@ss 5.1	27141134
eCl@ss 6.0	27141134
eCl@ss 7.0	27141134
eCl@ss 8.0	27141134
eCl@ss 9.0	27141134

ETIM

ETIM 2.0	EC001283
ETIM 3.0	EC001283
ETIM 4.0	EC001283
ETIM 5.0	EC001283

UNSPSC

UNSPSC 6.01	30211811



Classifications

UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

٨	n	n	r	٠,	,,	۱,
н	U	D	1 (J١	/a	เร

Approvals

Approvals

CSA / KEMA-KEUR / PRS / IECEE CB Scheme / EAC / cULus Recognized / EAC

Ex Approvals

Approvals submitted

Approval details

CSA 1		
mm²/AWG/kcmil	22-10	
Nominal current IN	30 A	
Nominal voltage UN	300 V	

KEMA-KEUR KETA		
mm²/AWG/kcmil	4	
Nominal current IN	32 A	
Nominal voltage UN	250 V	

PRS		



Approvals

IECEE CB Scheme CB		
mm²/AWG/kcmil	4	
Nominal current IN	32 A	
Nominal voltage UN	250 V	


EAC

cULus Recognized				
	В	D		
mm²/AWG/kcmil	30-10	30-10		
Nominal current IN	30 A	10 A		
Nominal voltage UN	300 V	300 V		


EAC

Drawings

Dimensional drawing







Phoenix Contact 2016 $\ensuremath{@}$ - all rights reserved http://www.phoenixcontact.com