

Ground modular terminal block - OTTA 6-PE - 0790527


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective conductor universal terminal block with bolt connection, cross section: 0.1 - 6 mm², width: 11 mm, color: Green-yellow



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 005634
Weight per Piece (excluding packing)	34.39 g
Custom tariff number	85369010
Country of origin	India

Technical data

Environmental Product Compliance

REACH SVHC	4-Nonylphenol, ethoxylated
------------	----------------------------

General

Number of levels	1
Number of connections	2
Nominal cross section	6 mm ²
Color	green-yellow
Insulating material	PA
Flammability rating according to UL 94	V0
Rated surge voltage	8 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-2

Ground modular terminal block - OTTA 6-PE - 0790527

Technical data

General

Open side panel	No
-----------------	----

Dimensions

Length	43.5 mm
Width	12 mm
Height NS 35/7,5	52 mm
Height NS 35/15	59.5 mm
Height NS 32	57 mm

Connection data

Conductor cross section solid min.	0.1 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section flexible min.	0.1 mm ²
Conductor cross section flexible max.	6 mm ²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	10
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm
Connection method	Bolt connection
Connection in acc. with standard	DIN 46 234
Min. cross section	0.1 mm ²
Max. cross section	6 mm ²
Hole diameter	4.3 mm
Bolt diameter	4 mm
Connection in acc. with standard	DIN 46237
Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²
Hole diameter	4.3 mm
Bolt diameter	4 mm

Standards and Regulations

Connection in acc. with standard	CSA
	IEC 60947-7-2
	DIN 46 234
	DIN 46237
Flammability rating according to UL 94	V0

Ground modular terminal block - OTTA 6-PE - 0790527

Classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141141
eCl@ss 7.0	27141141
eCl@ss 8.0	27141141
eCl@ss 9.0	27141141

ETIM

ETIM 2.0	EC000901
ETIM 3.0	EC000901
ETIM 4.0	EC000901
ETIM 5.0	EC000901

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

CSA / UL Recognized / PRS / EAC


Ex Approvals


Approvals submitted

Approval details

Ground modular terminal block - OTTA 6-PE - 0790527

Approvals

CSA 	
mm ² /AWG/kcmil	22-10

UL Recognized 

PRS

EAC

Drawings

Circuit diagram

