

Sealing frame - CES-B16-SFFS-PLBK - 0801659

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sealing frame with screw locking, size B16, with flat gasket, for 8 small sleeves



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	140.0 g
Custom tariff number	85472000
Country of origin	Poland

Technical data

Dimensions

Length	120 mm
Width	58.5 mm
Height	20 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Frame type	Sealing frame
Material	PA
Inflammability class according to UL 94	V0
Color	black
Torque	2 Nm ... 4 Nm (Locking screw)
Installation instructions	M4 locking screw with 3 mm Allen screw head, 2 ... 4 Nm torque, 1 large sleeve requires the space of 4 small sleeves, M4 mounting screw, 1.8 Nm torque for mounting screws
	Leak-tightness is guaranteed with underwall and perpendicular mounting; the CES-B24-WRG-BK flat gasket (supplied as standard) should be

Sealing frame - CES-B16-SFFS-PLBK - 0801659

Technical data

General

	inserted between the wall and the sealing frame in the case of wall mounting.
--	-------------------------------------------------------------------------------

Classifications

eCl@ss

eCl@ss 4.0	23110102
eCl@ss 4.1	23110102
eCl@ss 5.0	23110102
eCl@ss 5.1	23110102
eCl@ss 6.0	23110102
eCl@ss 7.0	23110102

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC002498

UNSPSC

UNSPSC 6.01	27113201
UNSPSC 7.0901	27113201
UNSPSC 11	27113201
UNSPSC 12.01	27113201
UNSPSC 13.2	27113201

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / GL / cULus Recognized

Ex Approvals

Approvals submitted

Sealing frame - CES-B16-SFFS-PLBK - 0801659

Approvals

Approval details

UL Recognized


cUL Recognized

GL

cULus Recognized


Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Panel cutout