

## DIN rail perforated - NS 35/15 WH PERF 2000MM - 0806602


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, color: silver



### Key Commercial Data

Packing unit	1 M
Minimum order quantity	5 M
GTIN	 4 017918 167424
GTIN	4017918167424
Weight per Piece (excluding packing)	645.000 g
Custom tariff number	72166190
Country of origin	Germany

### Technical data

#### Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm
Hole width	15.00 mm
Hole height	6.20 mm
Drill hole spacing	25.00 mm

#### General

Material	Steel
Coating	Galvanized, white passivated
Color	silver

# DIN rail perforated - NS 35/15 WH PERF 2000MM - 0806602


## Technical data

### Standards and Regulations

Test standard	similar to EN 60715
Connection in acc. with standard	IEC / EN

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

### UNSPSC

UNSPSC 6.01	30212109
-------------	----------

## DIN rail perforated - NS 35/15 WH PERF 2000MM - 0806602

### Classifications

#### UNSPSC

UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708