

Cable gland - HC-B-G-M25-EC-AL - 1411446

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



EVO EMC cable gland with bayonet locking, B series, size M25, cable diameter: 11 - 16 mm

Product Description

Metal cable gland



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	80.0 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Wrench size, union nut	27 mm
External cable diameter	11 mm ... 16 mm

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 125 °C (static)

General

Type of the screw connection	M25
Material	Die-cast aluminum, corrosion-resistant
Housing material	Die-cast aluminum, corrosion resistant
Cable gland material	Aluminum
Material, pressure screw	Nickel-plated brass

Cable gland - HC-B-G-M25-EC-AL - 1411446

Technical data

General

Seal material	NBR
Cable seal material	NBR
Shielded	Yes
Thread type on connection side	Bayonet B metal
Thread type on seal side	M25
Tightening torque, union nut	7.50 Nm

Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 4.0	EC000441
ETIM 5.0	EC000441

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted


Approval details

EAC

Drawings

Cable gland - HC-B-G-M25-EC-AL - 1411446

Dimensional drawing



Dimensional drawing

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>