

Terminal strip marker carrier - KLM 2 - 0807575

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Terminal strip marker carrier, gray, unlabeled, Mounting type: Plug in, Lettering field: 20 mm x 8 mm

Product Features

- The KLM range has been specifically developed for CLIPFIX end brackets
- The precise engagement mechanism enables infinite adjustment of the labeling area height
- Smaller labeling markers up to the maximum lettering field size can also be mounted side by side

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	0.545 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	22 mm
Width (a)	12.5 mm
Height	42 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	gray
Components	Halogen-free
Flammability rating according to UL 94	V2
Material	PA
Marking mounting type	Plug in

Standards and Regulations

Terminal strip marker carrier - KLM 2 - 0807575

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410