

Power cable - SAC-4P-FSS/10,0-PUR PE SH SCO - 1424099

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power cable, 4-position, PUR halogen-free, Orange (RAL 2003), matt, shielded, free cable end, on Socket straight M12 SPEEDCON, S-coded, Cable length: 10 m, for AC current up to 12 A/630 V

Why buy this product

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ High-performance: AC connectors for up to 12 A and 630 V AC
- ✓ Protection against incorrect connection using special S-coding
- ✓ Shield power reliably – 360° shielding to reduce electromagnetic loads
- ✓ Save time, thanks to installation with SPEEDCON fast locking system
- ✓ Our standard: robust halogen-free PUR cable



Key Commercial Data

| | |
|--------------------------------------|-------------|
| Packing unit | 1 STK |
| Weight per Piece (excluding packing) | 1,520.000 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-----------------|------|
| Length of cable | 10 m |
|-----------------|------|

Ambient conditions

| | |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |
| Degree of protection | IP65 |
| | IP67 |

General

| | |
|-----------------------|------|
| Rated current at 40°C | 12 A |
|-----------------------|------|

Power cable - SAC-4P-FSS/10,0-PUR PE SH SCO - 1424099

Technical data

General

| | |
|------------------------------|---------------|
| Rated voltage | 630 V |
| Rated surge voltage | 1.5 kV |
| Number of positions | 4 |
| Insulation resistance | ≤ 10 GΩ |
| Coding | S power |
| Standards/regulations | M12 connector |
| Status display | No |
| Protective circuit/component | Unwired |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Insertion/withdrawal cycles | > 100 |

Material

| | |
|--|---|
| Flammability rating according to UL 94 | V0 |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Material, knurls | Zinc die-cast, nickel-plated |

Standards and Regulations

| | |
|--|---------------|
| Standard designation | M12 connector |
| Flammability rating according to UL 94 | V0 |

Cable

| | |
|-------------------------------------|--|
| Cable type | PUR halogen-free orange shielded |
| Cable type (abbreviation) | PUR |
| Cable abbreviation | 9YSLC11Y-JZ |
| UL AWM style | 20234 / 10492 (80°C/1000 V) |
| Conductor cross section | 4x 1.5 mm ² |
| AWG power supply | 16 |
| Conductor structure, voltage supply | 78x 0.15 mm |
| Core diameter including insulation | ≤ 2.5 mm |
| Thickness, insulation | 0.4 mm |
| Wire colors | Black 1, black 2, black 3, green/yellow |
| Overall twist | 4 wires optimally twisted |
| Shielding | Tinned copper-braided shield, approx. 85% covering |
| External sheath, color | orange RAL 2003 |
| Outer sheath thickness | 1.2 mm |

Power cable - SAC-4P-FSS/10,0-PUR PE SH SCO - 1424099

Technical data

Cable

| | |
|---|---|
| External cable diameter D | 9.7 mm ±0,3 mm |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 7.5 x D |
| Number of bending cycles | 4000000 |
| Minimum bending radius, drag chain applications | 10 x D |
| Traversing path | 10 m |
| Traversing rate | 3 m/s |
| Acceleration | 10 m/s ² |
| Torsion force | ± 25 °/m |
| Outer sheath, material | PUR |
| Material conductor insulation | PP |
| Conductor material | Bare Cu litz wires |
| Insulation resistance | ≥ 10 MΩ*km (at 20 °C) |
| Conductor resistance | ≤ 13.3 Ω/km (at 20 °C) |
| Nominal voltage, cable | 1000 V AC |
| Test voltage, cable | 4260 V AC (5 min.) |
| Flame resistance | According to EN 60332-1-2 |
| | in acc. to UL 1581 VW1 |
| | According to CSA C 22.2 No. 210-05 FT1 |
| Halogen-free | According to VDE 0282-13 Appendix C |
| Resistance to oil | in accordance with DIN EN 60811-2-1 |
| | According to DIN EN 50363-10-2 |
| Other resistance | UV resistant |
| | Low adhesion |
| Ambient temperature (operation) | -40 °C ... 90 °C (cable, fixed installation) |
| | -30 °C ... 90 °C (cable, flexible installation) |

Environmental Product Compliance

| | |
|------------|-----------------|
| REACH SVHC | DOTe 15571-58-1 |
|------------|-----------------|

Drawings


Power cable - SAC-4P-FSS/10,0-PUR PE SH SCO - 1424099

Schematic diagram




Pin assignment of M12 socket, 4-pos., S-coded, socket side view

Cable cross section




PUR halogen-free orange shielded [PUR]

Dimensional drawing



M12 x 1 socket, straight

Circuit diagram



Contact assignment of the M12 socket

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed


Ex Approvals


Approval details

| | |
|---|-------|
| UL Listed http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm FILE E 468743 | |
| mm ² /AWG/kcmil | 16 |
| Nominal current I _N | 12 A |
| Nominal voltage U _N | 600 V |

Power cable - SAC-4P-FSS/10,0-PUR PE SH SCO - 1424099

Approvals

| | |
|--|-------|
| cUL Listed  http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm FILE E 468743 | |
| mm ² /AWG/kcmil | 16 |
| Nominal current I _N | 12 A |
| Nominal voltage U _N | 600 V |

| | |
|--|--|
| cULus Listed  | |
|--|--|