

Power cable - SAC-4P-MST/ 5,0-PUR SH SCO - 1424122

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power cable, 4-position, PUR halogen-free, black RAL 9005, shielded, Plug straight M12 SPEEDCON, T-coded, on free cable end, Cable length: 5 m, for direct current up to 12 A/60 V

Product Features

- Easy and safe: 100% electrically tested plug-in components
- High-performance: DC connectors for up to 12 A and 60 V DC
- Protection against incorrect connection using special T-coding
- Shield power reliably – 360° shielding to reduce electromagnetic loads
- Save time, thanks to installation with SPEEDCON fast locking system
- Our standard: robust halogen-free PUR cable



Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Weight per Piece (excluding packing) | 780.0 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-----------------|-----|
| Length of cable | 5 m |
|-----------------|-----|

Ambient conditions

| | |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |
| Degree of protection | IP65 |
| | IP67 |

General

| | |
|-----------------------|------|
| Rated current at 40°C | 12 A |
|-----------------------|------|

Power cable - SAC-4P-MST/ 5,0-PUR SH SCO - 1424122

Technical data

General

| | |
|------------------------------|------------------------|
| Rated voltage | 60 V |
| Rated surge voltage | 1.5 kV |
| Number of positions | 4 |
| Insulation resistance | ≤ 10 GΩ |
| Coding | T power |
| Standards/regulations | M12 connector |
| Status display | No |
| Protective circuit/component | Unwired |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Insertion/withdrawal cycles | > 100 |
| Torque | 0.4 Nm (M12 connector) |

Material

| | |
|--|---|
| Flammability rating according to UL 94 | V0 |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Material, knurls | Zinc die-cast, nickel-plated |

Standards and Regulations

| | |
|--|---------------|
| Standard designation | M12 connector |
| Flammability rating according to UL 94 | V0 |

Cable

| | |
|---|--|
| Cable type | PUR halogen-free black |
| Cable type (abbreviation) | PUR |
| Cable abbreviation | LS9YC11Y-OB |
| Conductor cross section | 4x 1.5 mm ² |
| AWG power supply | 16 |
| Core diameter including insulation | 2.4 mm |
| Thickness, insulation | 1.2 mm (Outer cable sheath) |
| Wire colors | brown, white, blue, black |
| Overall twist | 4 wires optimally twisted |
| Shielding | Tinned copper-braided shield, approx. 85% covering |
| External sheath, color | black RAL 9005 |
| External cable diameter D | 9.7 mm ±0,3 mm |
| Smallest bending radius, fixed installation | 49 mm |

Power cable - SAC-4P-MST/ 5,0-PUR SH SCO - 1424122

Technical data

Cable

| | |
|---|---|
| Smallest bending radius, movable installation | 73 mm |
| Number of bending cycles | 4000000 |
| Bending radius | 97 mm |
| Traversing path | 10 m |
| Traversing rate | 3 m/s |
| Acceleration | 10 m/s ² |
| Torsion force | ± 25 °/m |
| Outer sheath, material | PUR |
| Material conductor insulation | PP |
| Conductor material | Bare Cu litz wires |
| Insulation resistance | ≥ 10 MΩ*km (at 20 °C) |
| Conductor resistance | ≤ 13.3 Ω/km (at 20 °C) |
| Nominal voltage, cable | 300 V AC |
| Test voltage, cable | 1500 V AC (5 min.) |
| Flame resistance | According to EN 60332-1-2 |
| | in acc. to UL 1581 VW1 |
| Halogen-free | According to VDE 0282-13 Appendix C |
| Resistance to oil | in accordance with DIN EN 60811-2-1 |
| | According to DIN EN 50363-10-2 |
| Ambient temperature (operation) | -40 °C ... 90 °C (cable, fixed installation) |
| | -30 °C ... 90 °C (cable, flexible installation) |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140815 |
| eCl@ss 4.1 | 27140815 |
| eCl@ss 5.0 | 27143423 |
| eCl@ss 5.1 | 27143423 |
| eCl@ss 6.0 | 27143423 |
| eCl@ss 7.0 | 27449001 |
| eCl@ss 8.0 | 27279218 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC002061 |
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC001855 |

Power cable - SAC-4P-MST/ 5,0-PUR SH SCO - 1424122

Classifications

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11 | 31251501 |
| UNSPSC 12.01 | 31251501 |
| UNSPSC 13.2 | 31251501 |

Approvals

Approvals


Approvals


UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approvals submitted

Approval details

| | |
|---|------|
| UL Listed  | |
| mm ² /AWG/kcmil | 16 |
| Nominal current I _N | 12 A |
| Nominal voltage U _N | 63 V |

| | |
|--|------|
| cUL Listed  | |
| mm ² /AWG/kcmil | 16 |
| Nominal current I _N | 12 A |
| Nominal voltage U _N | 63 V |


Power cable - SAC-4P-MST/ 5,0-PUR SH SCO - 1424122

Approvals




Drawings

Schematic diagram




Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

Cable cross section




PUR halogen-free black [PUR]

Dimensional drawing



M12 x 1 plug, straight

Circuit diagram



Contact assignment of the M12 plug