

Device marker - US-EMSP (90X60) - 0828788

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Device marker, Card, white, unlabeled, can be labeled with: THERMOMARK CARD, Mounting type: Screws, rivets, Lettering field: 90 x 60 mm



The illustration shows a version of the product

Product Features

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-EMSP ... UniSheet labeling range includes markers that can be attached using screws or rivets
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	14.0 g
Custom tariff number	39204910
Country of origin	Germany

Technical data

Dimensions

Length (b)	100 mm
Width (a)	60 mm
Height	0.5 mm
Hole diameter	3.20 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
---------------------------------	------------------

General

Color	white
Components	Silicone-free

Device marker - US-EMSP (90X60) - 0828788

Technical data

General

Flammability rating according to UL 94	V0
Material	PVC
	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2
Number of individual labels per row	1
Marking mounting type	Screws, rivets

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27149129

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410