

Cable gland - HC-M-KV-M32(19-27) - 1646010


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Metal screw connection up to 5 bar, thread length: 8 mm, cable diameter: 19 - 27 mm, WAF 43, screw connection: M32



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 941253
Weight per Piece (excluding packing)	131.17 g
Custom tariff number	74199990
Country of origin	Germany

Technical data

Dimensions

Length	32 mm
Length without connecting thread	24 mm
Connecting thread diameter	32 mm
Wrench size, union nut	43 mm
Wrench size, support	43 mm
Hexagon angular dimension GRP	46 mm
Length of the connecting thread	8 mm
External cable diameter	19 mm ... 27 mm

Ambient conditions

Degree of protection	IP65
	IP65
Ambient temperature (operation)	-30 °C ... 100 °C

Cable gland - HC-M-KV-M32(19-27) - 1646010

Technical data

General

No. of conductors	1
Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
O-ring material	NBR
Shielded	No
Thread type on connection side	M32
Tightening torque, union nut	15.00 Nm
Color	silver

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Cable gland - HC-M-KV-M32(19-27) - 1646010

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Dimensional drawing

