

## Electrical crimping tool - CF 500-120V - 1208351

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Universal electric crimper to take dies for a wide variety of contact elements

The figure shows the CF 500-230V version

### Product Features

- Ferrules up to 50 mm<sup>2</sup>
- Uninsulated cable lugs up to 6 mm<sup>2</sup>
- Turned contacts up to 10 mm<sup>2</sup>
- TWIN ferrules up to 2 x 10 mm<sup>2</sup>
- Insulated cable lugs up to 6 mm<sup>2</sup>
- Tube lugs up to 10 mm<sup>2</sup>

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	13000.0 g
Custom tariff number	84798100
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	220 mm
Width (a)	140 mm
Height	320 mm

#### General

Compression	universal
Power consumption	160 VA

# Electrical crimping tool - CF 500-120V - 1208351

## Classifications

### eCl@ss

eCl@ss 4.0	21043074
eCl@ss 4.1	21043074
eCl@ss 5.0	21043290
eCl@ss 5.1	21059090
eCl@ss 6.0	17130101
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101
eCl@ss 9.0	17130101

### ETIM

ETIM 3.0	EC000168
ETIM 4.0	EC000168
ETIM 5.0	EC002778

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

