

Crimp contact - CK4,0-ED-6,00ST AG - 1663268


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Turned 4.0 crimp contact, individual male contact, core diameter 6.00 mm², silver-plated



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 017918 123079
Weight per Piece (excluding packing)	3.288 g
Custom tariff number	74152900
Country of origin	Germany

Technical data

Electrical characteristics

Note	For HC-M-3 modules
------	--------------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Conductor cross section	6 mm ²
Connection cross section AWG	10
Stripping length of the individual wire	9.6 mm
Insertion/withdrawal cycles	≥ 500

General

Type	Individual male contact
Series	HC-M-03

Crimp contact - CK4,0-ED-6,00ST AG - 1663268

Technical data

General

Connection method	Crimp connection
-------------------	------------------

Material data

Contact material	Copper alloy
Contact surface material	silver-plated

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

EAC / EAC

Crimp contact - CK4,0-ED-6,00ST AG - 1663268

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC

EAC

Drawings

Dimensional drawing

