

## Pointed pliers - UNIFOX-PE VDE - 1212529

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Needle-nose pliers, angled design, with opening spring and locking device, finely notched grip area, stripping possible for 1.5 mm<sup>2</sup> and 2.5 mm<sup>2</sup>, integrated M8 - M10 ring wrench, VDE 1000 V AC/1500 V DC tested

### Product Features

- The tools feature ergonomic two-component safety handles
- Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	300.0 g
Custom tariff number	82032000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	200 mm
------------	--------

#### General

Color	black
Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745

#### Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745

### Classifications

#### eCl@ss

eCl@ss 4.0	21040302
------------	----------

# Pointed pliers - UNIFOX-PE VDE - 1212529

## Classifications

### eCl@ss

eCl@ss 4.1	21040302
eCl@ss 5.0	21040302
eCl@ss 5.1	21040302
eCl@ss 6.0	21049011
eCl@ss 7.0	21049011
eCl@ss 8.0	21043817

### ETIM

ETIM 4.0	EC000833
ETIM 5.0	EC000833

### UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	23171604

## Approvals

### Approvals

---

Approvals

VDE Zeichengenehmigung / EAC

---


Ex Approvals

---

Approvals submitted

---

### Approval details

VDE Zeichengenehmigung 
--

EAC
-----

