

## Screwdriver - SF-SL 0,6X3,5-100 - 1212549

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, bladed (lasered), size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

The figure shows the SZF 1 version

### Your advantages

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589840
GTIN	4046356589840
Weight per Piece (excluding packing)	42.000 g
Custom tariff number	82054000
Country of origin	Czech Republic

### Technical data

#### Dimensions

Length (b)	181 mm
Width (a)	26 mm
Blade thickness	0.6 mm
Blade width	3.5 mm
Blade height	100 mm
Wrench size	0 mm

#### General

Type	Bladed
	straight
Material	alloyed tool steel

## Screwdriver - SF-SL 0,6X3,5-100 - 1212549

### Technical data

#### General

Test standard	DIN/ISO 2380-1
---------------	----------------

#### Standards and Regulations

Test standard	DIN/ISO 2380-1
---------------	----------------


#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Drawings

# Screwdriver - SF-SL 0,6X3,5-100 - 1212549

Pictogram



## Classifications

eCl@ss

eCl@ss 10.0.1	21040407
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21040400
eCl@ss 7.0	21040407

# Screwdriver - SF-SL 0,6X3,5-100 - 1212549

## Classifications

### eCl@ss

eCl@ss 8.0	21040407
eCl@ss 9.0	21040407

### ETIM

ETIM 2.0	EC000158
ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC000158
ETIM 6.0	EC000158
ETIM 7.0	EC000158

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701
UNSPSC 18.0	27111701
UNSPSC 19.0	27111701
UNSPSC 20.0	27111701
UNSPSC 21.0	27111701

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

