

Screwdriver - SF-SL 0,6X3,5-200 - 1212550

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, slot-headed, size: 0.6 x 3.5 x 200 mm, 2-component grip, with non-slip grip

Your advantages

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589857
GTIN	4046356589857
Weight per Piece (excluding packing)	42.000 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	281 mm
Width (a)	26 mm
Blade thickness	0.6 mm
Blade width	3.5 mm
Blade height	200 mm
Wrench size	0 mm

General

Type	Bladed
	straight
Material	alloyed tool steel
Test standard	DIN/ISO 2380-1

Screwdriver - SF-SL 0,6X3,5-200 - 1212550

Technical data

Standards and Regulations


Test standard	DIN/ISO 2380-1
---------------	----------------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Drawings

Pictogram



Screwdriver - SF-SL 0,6X3,5-200 - 1212550

Classifications

eCl@ss

eCl@ss 10.0.1	21040407
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21040400
eCl@ss 7.0	21040407
eCl@ss 8.0	21040407
eCl@ss 9.0	21040407

ETIM

ETIM 2.0	EC000158
ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC000158
ETIM 6.0	EC000158
ETIM 7.0	EC000158

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701
UNSPSC 18.0	27111701
UNSPSC 19.0	27111701
UNSPSC 20.0	27111701
UNSPSC 21.0	27111701

Approvals

Approvals

Approvals

EAC

Ex Approvals

Screwdriver - SF-SL 0,6X3,5-200 - 1212550

Approvals

Approval details

EAC



RU C-
DE.AI30.B.01750