

Screwdriver - SF-SL 0,6X3,5-100 S-VDE - 1212587

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Actuation tool, for ST terminal blocks, VDE insulated, with slimmer insulation integrated in the blade, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Product Features

- VDE-tested, for maximum safety
- In addition to standard applications, SF-SL ... screwdrivers are particularly suitable for modular terminal block assembly
- Because the insulation runs into the shaft, there is no protruding edge



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	43.4 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	181 mm
Width (a)	26 mm
Blade thickness	0.6 mm
Blade width	3.5 mm
Blade height	100 mm

General

Type	Bladed
	Straight
Material	Alloyed tool steel
Test standard	DIN/ISO 2380-1 IEC 60900:2004

Standards and Regulations

Screwdriver - SF-SL 0,6X3,5-100 S-VDE - 1212587

Technical data

Standards and Regulations

Test standard	DIN/ISO 2380-1 IEC 60900:2004
---------------	-------------------------------

Classifications

eCl@ss

eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402
eCl@ss 5.1	21040402
eCl@ss 6.0	21040290
eCl@ss 7.0	21040290
eCl@ss 8.0	21040407

ETIM

ETIM 4.0	EC000158
ETIM 5.0	EC000158

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals

Approvals

VDE Zeichengenehmigung / EAC

Ex Approvals

Approvals submitted

Screwdriver - SF-SL 0,6X3,5-100 S-VDE - 1212587

Approvals

Approval details

VDE Zeichengenehmigung

EAC

Drawings

Pictogram



Dimensional drawing



