

Crimping pliers - CRIMPFOX CENTRUS 10H - 1213156

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 10 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Why buy this product

- ☑ With a particularly small handle width, the tool fits perfectly in your hand
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping
- ☑ Pressure lock ensures consistently high quality crimping results





Key Commercial Data

Packing unit	1 STK
GTIN	4 055626 212630
GTIN	4055626212630
Weight per Piece (excluding packing)	480.000 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	180 mm
Width (a)	70 mm

General



Crimping pliers - CRIMPFOX CENTRUS 10H - 1213156

Technical data

General

Color	black
Compression	HEX crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Min. cross section	0.14 mm²
Max. cross section	10 mm ²
AWG min	26
AWG max	8

Approvals	
Approvals	
Approvals	
EAC	
Ex Approvals	
Approval details	
EAC EAC-Zulassung	

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com