

Network cable - VS-M12MSD-M12MSD-93E-CO/0,5 - 1401599

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Network cable, Ethernet, 4-position, PUR, water blue RAL 5021, shielded, Plug straight M12, Coding: D, on Plug straight M12, Coding: D, Cable length: 0.5 m



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 046356 566667
GTIN	4046356566667
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	85444210
Country of origin	Poland

Technical data

Dimensions

Length of cable	0.5 m
-----------------	-------

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

General data

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	4

Network cable - VS-M12MSD-M12MSD-93E-CO/0,5 - 1401599

Technical data

General data

Signal type/category	Ethernet
Overvoltage category	II
Degree of pollution	3
	3

Characteristics head 1

Head type	Plug straight M12
Coding	D (Data)

Characteristics head 2

Head type	Plug straight M12
Coding	D (Data)

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Cable

Cable type	Ethernet
Cable type (abbreviation)	930
Conductor cross section	0.25 mm ²
AWG signal line	24
Conductor structure signal line	7x 0.20 mm
Core diameter including insulation	1.4 mm
Wire colors	White-green, white-orange
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	2 cores with 2 fillers to the core
Shielding	Braided shielding made of galvanized copper wires
Optical shield covering	65 %
External sheath, color	water blue RAL 5021
Smallest bending radius, fixed installation	min. 40 mm
Smallest bending radius, movable installation	min. 40 mm
Cable weight	54 kg/km
Outer sheath, material	PUR
Material conductor insulation	Cell PE
Conductor material	Bare Cu litz wires
Insulation resistance	5 GΩ*km
Conductor resistance	84 mΩ/m
Working capacitance	42.5 pF

Network cable - VS-M12MSD-M12MSD-93E-CO/0,5 - 1401599


Technical data

Cable

Wave impedance	100 Ω \pm 5 %
Signal speed	0.72 c
Signal runtime	46 ns/m
Shield attenuation	60 dB (Up to 1000 MHz)
Interference suppression	90 dB (Up to 1000 MHz)
Nominal voltage, cable	125 V
Test voltage, cable	1000 V
Ambient temperature (operation)	-20 °C ... 70 °C (cable, fixed installation)
	0 °C ... 50 °C (cable, flexible installation)


Drawings

Schematic diagram




Pin assignment M12 male connector, 4-pos., D-coded, male side

Cable cross section



Ethernet [930]

Dimensional drawing



Plug, M12 x 1, straight, shielded