

Adapter - HC-NPT-1/1-M32 - 1686863

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



NPT adapter, IP68, up to 5 bar, incl. O-ring seal, M32 to 1"



Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 822729
GTIN	4017918822729
Weight per Piece (excluding packing)	101.900 g
Custom tariff number	74199990
Country of origin	Germany

Technical data

Dimensions

Length	33 mm
Length without connecting thread	25 mm
Connecting thread diameter	32 mm
Length of the connecting thread	8 mm

Ambient conditions

Degree of protection	IP68 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Brass, nickel-plated
Cable gland material	Nickel-plated brass

Adapter - HC-NPT-1/1-M32 - 1686863

Technical data

General


O-ring material	NBR
Thread type connection side	M32
Thread type on seal side	1/1" NPT
Color	silver

Environmental Product Compliance


China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27439207
eCl@ss 9.0	27430314

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938

Adapter - HC-NPT-1/1-M32 - 1686863

Classifications

ETIM

ETIM 6.0	EC000938
----------	----------

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------
