

RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 coupling, Degree of protection: IP20, Number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), Material: Copper alloy, for VS-08 and push-pull panel mounting frames

Freenet insert



Ethernet



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	20.0 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Number of positions	8
Number of slots	2
Insertion/withdrawal cycles	>= 100

Ambient conditions

Degree of protection	IP20
----------------------	------

Material data

Housing material	Copper alloy
------------------	--------------

Electrical characteristics

Number of positions	8
---------------------	---

Classifications

eCl@ss

eCl@ss 4.0	272607xx
------------	----------

RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617

Classifications

eCl@ss

eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309

ETIM

ETIM 3.0	EC001134
ETIM 4.0	EC001134
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	31261501
UNSPSC 13.2	39121712

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approvals submitted

Approval details


EAC

EAC


Drawings

RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617

Dimensional drawing




Schematic diagram




RJ45 socket insert, Freenet system

Schematic diagram



Schematic diagram



Schematic diagram

