

## Cable gland - HC-B-G-M32-PLRBK - 1407671

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



EVO plastic cable gland with bayonet locking, for housing series B, size M32, cable diameter: 11 ... 21 mm

### Product Description

Plastic cable gland



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	60.0 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Wrench size, union nut	30 mm
External cable diameter	11 mm ... 21 mm

#### Ambient conditions

Degree of protection	IP66 (DIN IEC 60529)
	4 (UL50e / NEMA 250)
	4X (UL50e / NEMA 250)
	12 (UL50e / NEMA 250)
Ambient temperature (operation)	-40 °C ... 100 °C

#### General

Type of the screw connection	M32
No. of conductors	1
Material	PA
Cable gland material	Polyamide

# Cable gland - HC-B-G-M32-PLRBK - 1407671

## Technical data

### General

Material, pressure screw	PBT
Seal material	NBR
Cable seal material	NBR
Shielded	No
Thread type on connection side	Bayonet B plastic
Tightening torque, union nut	7.50 Nm
Flammability rating according to UL 94	V0 / V2

### Standards and Regulations

Flammability rating according to UL 94	V0 / V2
--	---------

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27143424
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

### ETIM

ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

# Cable gland - HC-B-G-M32-PLRBK - 1407671

## Approvals

Approvals

EAC

---

Ex Approvals

---

Approvals submitted


---

## Approval details

EAC
-----

## Drawings

Dimensional drawing



Dimensional drawing

---