

Cable gland - G-INS-M20-S68N-PNES-GY - 1411125

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Cable gland material: Polyamide 6, External cable diameter 6 mm ... 12 mm, Shielding: No, Connecting thread: M20, Color: silver grey

The illustration shows version G-INS-M25-M68N-PNES-GY



Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Minimum order quantity | 5 pc |
| Weight per Piece (excluding packing) | 12.0 g |
| Custom tariff number | 39269097 |
| Country of origin | Turkey |

Technical data

Dimensions

| | |
|----------------------------------|----------------|
| Length | 42.3 mm |
| Length without connecting thread | 32.3 mm |
| Connecting thread diameter | 20 mm |
| Wrench size, union nut | 24 mm |
| Wrench size, support | 24 mm |
| Hexagon angular dimension GRP | 27.8 mm |
| Length of the connecting thread | 10 mm |
| External cable diameter | 6 mm ... 12 mm |

Ambient conditions

| | |
|---------------------------------|--|
| Degree of protection | IP68 |
| | IP65 (5 bar, 30 min.) |
| Ambient temperature (operation) | -30 °C ... 80 °C (for a short period up to 150 °C) |

General

Cable gland - G-INS-M20-S68N-PNES-GY - 1411125

Technical data

General

| | |
|---|---------------------------|
| Cable gland material | Polyamide 6 |
| Seal material | Neoprene |
| Cable seal material | Neoprene |
| Shielded | No |
| Thread type on connection side | M20 |
| Torque | 5 Nm ... 6 Nm (Union nut) |
| Inflammability class according to UL 94 | V2 |
| Color | silver gray |
| | silver grey |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27149109 |
| eCl@ss 6.0 | 27149109 |
| eCl@ss 8.0 | 27149109 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000441 |
| ETIM 5.0 | EC000441 |

Approvals

Approvals

Approvals

CSA / UL Recognized / VDE Zeichengenehmigung


Ex Approvals

Approvals submitted

Approval details

Cable gland - G-INS-M20-S68N-PNES-GY - 1411125

Approvals



Drawings

Dimensional drawing

