

## Cable gland - HC-B-G-M32-EC-AL - 1411440

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



EVO EMC cable gland with bayonet locking, B series, size M32, cable diameter: 14 - 21 mm

### Product Description

Metal cable gland



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	100.0 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Wrench size, union nut	34 mm
External cable diameter	14 mm ... 21 mm

#### Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 125 °C (static)

#### General

Type of the screw connection	M32
Material	Die-cast aluminum, corrosion-resistant
Housing material	Die-cast aluminum, corrosion resistant
Cable gland material	Aluminum
Material, pressure screw	Nickel-plated brass

# Cable gland - HC-B-G-M32-EC-AL - 1411440

## Technical data

### General

Seal material	NBR
Cable seal material	NBR
Shielded	Yes
Thread type on connection side	Bayonet B metal
Thread type on seal side	M32
Tightening torque, union nut	10.00 Nm

## Classifications

### eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27149109
eCl@ss 8.0	27149109

### ETIM

ETIM 4.0	EC000441
ETIM 5.0	EC000441

## Approvals

### Approvals

---

### Approvals

### EAC

---

### Ex Approvals

---

### Approvals submitted

---


### Approval details

EAC
-----

## Drawings

## Cable gland - HC-B-G-M32-EC-AL - 1411440

Dimensional drawing



Dimensional drawing