

Cable gland - HC-B-G-M20-ER-AL - 1411442

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




EVO metal cable gland with bayonet locking, B series, size M20, cable diameter: 7 - 13 mm

Product Description

Metal cable gland

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 932417
GTIN	4046356932417
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Wrench size, union nut	22 mm
External cable diameter	9 mm ... 12 mm

Ambient conditions

Degree of protection	IP66
	IP67
	4X (UL 50)
Ambient temperature (operation)	-40 °C ... 125 °C (static)

General

Cable gland - HC-B-G-M20-ER-AL - 1411442

Technical data

General


Type of the screw connection	M20
No. of conductors	1
Material	Die-cast aluminum, corrosion-resistant
Housing material	Die-cast aluminum, corrosion resistant
Cable gland material	Aluminum
Material, pressure screw	Nickel-plated brass
Seal material	NBR
Cable seal material	NBR
Shielded	No
Thread type on connection side	Bayonet B metal
Tightening torque, union nut	7.50 Nm
Color	silver

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Dimensional drawing

Approvals

Approvals

Approvals

EAC / UL Recognized / cUL Recognized / cULus Recognized


Cable gland - HC-B-G-M20-ER-AL - 1411442

Approvals


Ex Approvals

Approval details

EAC 7500651.22.01.00246

UL Recognized  <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> E255026

cUL Recognized  <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> E255026

cULus Recognized  <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>