

RJ45 connector - CUC-IND-C1ZNI-S/R4IP8 - 1421126

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 connector, Degree of protection: IP20, Number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), Material: Zinc die-cast, Connection method: IDC fast connection, Connection cross section: AWG 23-22, Cable exit: straight

Why buy this product

- assembly without special tools
- One-Piece Design
- AWG 23-22
- 360° shielding
- High shock and vibration resistance



Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	40.000 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Number of positions	8
Connection profile	RJ45
Insertion/withdrawal cycles	≥ 750
Connection method	IDC fast connection
Conductor cross section	0.23 mm ² ... 0.32 mm ² (solid)
	0.23 mm ² ... 0.36 mm ² (stranded)
Connection cross section AWG	23 ... 22 (solid)
	23 ... 22 (stranded)

RJ45 connector - CUC-IND-C1ZNI-S/R4IP8 - 1421126

Technical data

Mechanical characteristics

Max. cable diameter	5 mm ... 9 mm
External cable diameter	5 mm ... 9 mm
Cable exit	straight
Wire diameter including insulation	≤ 1.6 mm
Degree of protection	IP20
Type	RJ45, IP20
No. of cable outlets	1

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
---------------------------------	------------------

Material data

Flammability rating according to UL 94	V0
Housing material	Zinc die-cast
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel

Electrical characteristics

Number of positions	8
Transmission speed	1 GBit/s
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
GRP transmission properties	CAT5 (IEC 11801:2002)
Transmission speed	1 Gbps
Frequency range	to 100 MHz
Rated current	1.75 A
Overvoltage category	I
Contact resistance	0.001 Ω (Wire – IDC)
	0.005 Ω (Litz wires – IDC)


Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Drawings

RJ45 connector - CUC-IND-C1ZNI-S/R4IP8 - 1421126

Dimensional drawing



RJ45 connector, IP20

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27261204
eCl@ss 7.0	27440205
eCl@ss 8.0	27440101
eCl@ss 9.0	27440101

ETIM

ETIM 5.0	EC002636
----------	----------

Accessories

Accessories

Data cable by the meter

Network cable - VS-OE-OE-93B-100,0 - 1416389



Network cable, PROFINET CAT5 (100 Mbps), 4-position, PVC, green RAL 6018, shielded, free cable end, on free cable end, Cable length: 100 m

RJ45 connector - CUC-IND-C1ZNI-S/R4IP8 - 1421126

Accessories

Network cable - VS-OE-OE-93B/... - 1417362



Network cable, PROFINET CAT5 (100 Mbps), 4-position, PVC, green RAL 6018, shielded, free cable end, on free cable end, Cable length: Free entry (0.5 ... 400.0 m)

Electronics pliers

Diagonal cutter - MICROFOX-SP-1 - 1212487



Electronic diagonal cutter, tapered head, without chamfer, with opening spring, non-reflective phosphate-treated surface, punched version

Terminal marking

Marker for terminal blocks - TMT 5 R - 0816430



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Perforated, Mounting type: Snap into universal marker groove, Snap into flat marker groove, for terminal block width: 5.2 mm, Lettering field: 6.4 x 5.15 mm

Marker for terminal blocks - TMT 5 R RD - 0816427



Marker for terminal blocks, Roll, red, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Perforated, Mounting type: Snap into universal marker groove, Snap into flat marker groove, for terminal block width: 5.2 mm, Lettering field: 6.4 x 5.15 mm

Marker for terminal blocks - TMT 5 R GN - 0816401



Marker for terminal blocks, Roll, green, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Perforated, Mounting type: Snap into universal marker groove, Snap into flat marker groove, for terminal block width: 5.2 mm, Lettering field: 6.4 x 5.15 mm

RJ45 connector - CUC-IND-C1ZNI-S/R4IP8 - 1421126

Accessories

Stripping tool - VS-CABLE-STRIP-VARIO - 1657407

Stripping tool, for the multi-level stripping of shielded cables

