

## Base strip - A-MSTBVA 2,5/ 6-G-5,08 - 1872509

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The illustration shows a 12-position version

Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 6, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Mounting: DIN rail



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	3.6 g
Custom tariff number	85366990
Country of origin	China

### Technical data

#### General

Color	green
Insulating material	PBT
Flammability rating according to UL 94	V0

#### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701

## Base strip - A-MSTBVA 2,5/ 6-G-5,08 - 1872509

### Classifications

#### eCl@ss

eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

#### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

### Approvals

#### Approvals

---

#### Approvals

EAC / cULus Recognized / EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

#### Approval details

EAC
-----

# Base strip - A-MSTBVA 2,5/ 6-G-5,08 - 1872509

## Approvals

cULus Recognized		
	B	D
Nominal current $I_N$	12 A	10 A
Nominal voltage $U_N$	300 V	300 V

EAC
-----

## Drawings

Dimensional drawing

