

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Sensor/actuator flush-type plug, 8-pos., M12, rear/screw mounting with Pg9 thread, with straight solder connection, high-grade steel version

### **Product Features**

Easy PCB assembly: one-piece connectors for wave soldering



## Key Commercial Data

Packing unit	1 pc
Minimum order quantity	20 pc
Weight per Piece (excluding packing)	16.69 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

#### Ambient conditions

Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)
	-40 °C 85 °C (without mechanical actuation)
Degree of protection	IP67
	IP69K

#### General

Note	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Rated current at 40°C	2 A
Rated voltage	30 V
Rated surge voltage	0.8 kV



# Technical data

#### General

Number of positions	8
Insulation resistance	$\geq$ 100 M $\Omega$
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Overvoltage category	Ш
Degree of pollution	3
Connection method	Solder pins
Insertion/withdrawal cycles	> 100
Torque	3 Nm 4 Nm (Installation-side)

### Material

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Stainless steel
Sealing material	NBR

#### Cable

Ambient temperature (operation)	-40 °C 85 °C (cable, fixed installation)
	-25 °C 85 °C (cable, flexible installation)

### Standards and Regulations

Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101
Flammability rating according to UL 94	V0

## Classifications

## eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440103
eCl@ss 9.0	27440102



# Classifications

## ETIM

ETIM 2.0	EC001297
ETIM 3.0	EC002061
ETIM 4.0	EC002062
ETIM 5.0	EC002061

## UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

# Approvals

### Approvals

Approvals

UL Recognized / EAC / cULus Recognized / EAC

Ex Approvals

Approvals submitted

#### Approval details

mm²/AWG/kcmil	26-20
Nominal current IN	2 A
Nominal voltage UN	30 V

EAC

ſ

٦





# Approvals

cULus Recognized	
mm²/AWG/kcmil	22
Nominal current IN	2 A
Nominal voltage UN	30 V

EAC


## Drawings





Mounting cutout with polarization for Pg9 thread

### Drilling diagram



M12 flush-type plug


Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

Dimensional drawing



M12 flush-type plug