

## Mounting material - HC-ALU 6 MOUNT 100 GY - 2200911

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Mounting foot for panel mounting the HC-ALU panel mounting base

### Product Features

- Item is from the HC-ALU product range
- Aluminum press-drawn section
- Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- Available in overall widths 53.5 mm ... 161 mm
- Degree of protection up to IP65
- Usable as handheld and wall housing
- Optional EMC seals available

### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 2 pc     |
| Weight per Piece (excluding packing) | 30.0 g   |
| Custom tariff number                 | 76161000 |
| Country of origin                    | Hungary  |

### Technical data

#### General

|              |                     |
|--------------|---------------------|
| Housing type | Panel mounting base |
| Color        | gray                |

#### Dimensions

|        |          |
|--------|----------|
| Length | 104.4 mm |
|--------|----------|

## Mounting material - HC-ALU 6 MOUNT 100 GY - 2200911

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27180401 |
| eCl@ss 4.1 | 27180401 |
| eCl@ss 5.0 | 27180506 |
| eCl@ss 5.1 | 27180506 |
| eCl@ss 6.0 | 27182003 |
| eCl@ss 7.0 | 27182701 |
| eCl@ss 8.0 | 27182701 |
| eCl@ss 9.0 | 27182701 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC002779 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11     | 31261501 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 31261501 |