

## FO connecting cable - VS-PC-2X-POF-980-SCRJ/FSMA-5 - 1657122


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled FO cable, break-out cable, polymer fiber 980/1000 µm, SC-RJ/IP20 on FSMA/IP20, for installation inside the control cabinets, the conductor is suitable for the UV-protected outside insert, length: 5 m



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 100182
GTIN	4046356100182
Weight per Piece (excluding packing)	76.000 g
Custom tariff number	85447000
Country of origin	Germany

### Technical data

#### Mechanical characteristics

Number of positions	2
Connection profile	SCRJ according to DIN EN 50377-6-1
Number of fibers	2
Insertion/withdrawal cycles	≥ 1000
Type of cable	Break-out cable
Degree of protection	IP20
	IP20

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Degree of protection	IP20

# FO connecting cable - VS-PC-2X-POF-980-SCRJ/FSMA-5 - 1657122

## Technical data

### Material data


Housing material	PBT/nickel silver
Outer sheath, material	PE
External sheath, color	black
Ferrule holder color	blue

### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings


Dimensional drawing



SC-RJ connector IP20

# FO connecting cable - VS-PC-2X-POF-980-SCRJ/FSMA-5 - 1657122

Schematic diagram



Pin assignment plug SCRJ

## Classifications

eCl@ss

eCl@ss 4.0	24010400
eCl@ss 4.1	24010400
eCl@ss 5.0	19030300
eCl@ss 5.1	19030300
eCl@ss 6.0	27061800
eCl@ss 7.0	27061803
eCl@ss 8.0	27061003
eCl@ss 9.0	27061003

ETIM

ETIM 3.0	EC000034
ETIM 4.0	EC001476
ETIM 5.0	EC001263
ETIM 6.0	EC001263
ETIM 7.0	EC001263

# FO connecting cable - VS-PC-2X-POF-980-SCRJ/FSMA-5 - 1657122

## Classifications

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	26121607

## Approvals

### Approvals

---

### Approvals

### EAC

---

### Ex Approvals

---

## Approval details

EAC		B.00767
-----	-------------------------------------------------------------------------------------	---------