

Uninterruptible power supply - QUINT-UPS/ 24DC/ 24DC/ 5/1.3AH - 2320254

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Uninterruptible power supply with IQ technology and integrated power storage for DIN rail mounting, input 24 V DC, output: 24 V DC/5 A, power storage: lead AGM 1.3 Ah, incl. mounted UTA 107/30 universal DIN rail adapter

Product Features

- Easy handling thanks to automatic battery detection, tool-free battery replacement during operation, and communication via the IFS interface
- Reliable starting of difficult loads with the static POWER BOOST power reserve with up to 1.5 times the nominal current permanently
- Fast tripping of standard circuit breakers with SFB (selective fuse breaking) technology
- Device suitable for universal use thanks to comprehensive license package and extensive parameterization and diagnostics options



Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Weight per Piece (excluding packing) | 2420.0 g |
| Custom tariff number | 85371091 |
| Country of origin | China |

Technical data

Dimensions

| | |
|--------|--------|
| Width | 88 mm |
| Height | 138 mm |
| Depth | 125 mm |

Ambient conditions

| | |
|--|-------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | 0 °C ... 40 °C |
| Ambient temperature (storage/transport) | -15 °C ... 40 °C |
| Max. permissible relative humidity (operation) | ≤ 95 % (25°C, non-condensing) |

Uninterruptible power supply - QUINT-UPS/ 24DC/ 24DC/ 5/1.3AH - 2320254

Technical data

Ambient conditions

| | |
|----------------|-------------------|
| Noise immunity | EN 61000-6-2:2005 |
|----------------|-------------------|

Input data

| | |
|--|---------------------|
| Nominal input voltage | 24 V DC |
| Input voltage range | 18 V DC ... 30 V DC |
| Current consumption (maximum) | 9.3 A (24 V DC) |
| Current consumption (idle) | 9.7 mA |
| Current consumption (charging process) | 1.7 A |
| Buffer period | 50 min. (1 A) |
| | 5 min. (5 A) |

Output data (24 V DC mains operation)

| | |
|---|---|
| Nominal output voltage | 24 V DC |
| Output voltage range (depends on the input voltage) | 18 V DC ... 30 V DC ($U_{OUT} = U_{IN} - 0.1 \text{ V DC}$) |
| Nominal output current (I_N) | 5 A (0 °C ... 40 °C) |
| POWER BOOST (I_{Boost}) | 7.5 A (-25 °C ... 40 °C) |
| Selective Fuse Breaking (I_{SFB}) | 30 A (-25 °C ... 60 °C) |

Output data (24 V DC battery operation)

| | |
|---|--|
| Nominal output voltage | 24 V DC |
| Output voltage range (depends on the input voltage) | 19.2 V DC ... 27.6 V DC ($U_{OUT} = U_{BAT} - 0.5 \text{ V DC}$) |
| Nominal output current (I_N) | 5 A (-25 °C ... 60 °C) |
| POWER BOOST (I_{Boost}) | 7.5 A (-25 °C ... 40 °C) |
| Selective Fuse Breaking (I_{SFB}) | 32.5 A (-25 °C ... 60 °C) |

General output data

| | |
|------------|--|
| Efficiency | > 97.1 % (Mains operation, with charged power storage) |
|------------|--|

General

| | |
|----------------------------------|---|
| IQ technology | Yes |
| Disposal | Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. They can also be returned to Phoenix Contact or the manufacturer. |
| Net weight | 2.2 kg |
| Memory medium | Lead rechargeable battery module 1.3 Ah |
| Protection class | III |
| MTTF/ MTBF (IEC 61709, SN 29500) | > 806000 h (40 °C) |
| Mounting position | horizontal DIN rail NS 35, EN 60715 |

Uninterruptible power supply - QUINT-UPS/ 24DC/ 24DC/ 5/1.3AH - 2320254

Technical data

General

| | |
|-----------------------|---|
| Assembly instructions | Can be aligned: horizontal 5 mm, vertical 50 mm |
|-----------------------|---|

Connection data, input

| | |
|---------------------------------------|----------------------------|
| Connection method | Pluggable screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section flexible min. | 0.2 mm ² |
| Conductor cross section flexible max. | 2.5 mm ² |
| Conductor cross section AWG min. | 20 |
| Conductor cross section AWG max. | 12 |
| Stripping length | 7 mm |
| Screw thread | M4 |

Connection data, output

| | |
|---------------------------------------|----------------------------|
| Connection method | Pluggable screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section flexible min. | 0.2 mm ² |
| Conductor cross section flexible max. | 2.5 mm ² |
| Conductor cross section AWG min. | 20 |
| Conductor cross section AWG max. | 12 |
| Stripping length | 7 mm |
| Screw thread | M4 |

Connection data for signaling

| | |
|---------------------------------------|---------------------|
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section flexible min. | 0.2 mm ² |
| Conductor cross section flexible max. | 2.5 mm ² |
| Conductor cross section AWG min. | 24 |
| Conductor cross section AWG max. | 12 |
| Screw thread | M4 |

Standards and Regulations

| | |
|----------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Shock | 30g in each direction, according to IEC 60068-2-27 |
| Noise immunity | EN 61000-6-2:2005 |
| Connection in acc. with standard | CUL |

Uninterruptible power supply - QUINT-UPS/ 24DC/ 24DC/ 5/1.3AH - 2320254

Technical data

Standards and Regulations

| | |
|--|---|
| Standards/regulations | EN 61000-4-3 |
| | EN 61000-4-4 |
| | EN 61000-4-6 |
| Standard - Electrical safety | EN 60950-1/VDE 0805 (SELV) |
| | EN 61558-2-17 |
| Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations | EN 50178/VDE 0160 (PELV) |
| UL approvals | UL/C-UL Recognized UL 60950 |
| | UL Listed UL 508 |
| Vibration (operation) | < 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6) |
| Low Voltage Directive | Conformance with LV directive 2006/95/EC |
| Rail applications | EN 50121-4 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27040702 |
| eCl@ss 4.1 | 27040702 |
| eCl@ss 5.0 | 27242213 |
| eCl@ss 5.1 | 27040603 |
| eCl@ss 6.0 | 27040603 |
| eCl@ss 7.0 | 27040603 |
| eCl@ss 8.0 | 27040603 |
| eCl@ss 9.0 | 27040705 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001039 |
| ETIM 4.0 | EC000382 |
| ETIM 5.0 | EC000382 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211510 |
| UNSPSC 7.0901 | 39121011 |
| UNSPSC 11 | 39121011 |
| UNSPSC 12.01 | 39121011 |
| UNSPSC 13.2 | 39121011 |

Uninterruptible power supply - QUINT-UPS/ 24DC/ 24DC/ 5/1.3AH - 2320254

Approvals

Approvals

Approvals

UL Recognized / UL Listed / cUL Recognized / cUL Listed / EAC / EAC / cULus Recognized / cULus Listed


Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approvals submitted

Approval details

UL Recognized 

UL Listed 

cUL Recognized 

cUL Listed 


EAC

EAC

cULus Recognized 

Uninterruptible power supply - QUINT-UPS/ 24DC/ 24DC/ 5/1.3AH - 2320254

Approvals



Drawings

Block diagram

