

Controller - ILC 171 ETH 2TX - 2700975

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Product Description

The ILC 171 ETH 2TX modular small-scale controller for the Inline I/O system is at the heart of Easy Automation. The ILC 1X1 series is characterized by its support for the Modbus/TCP and PROFINET Ethernet-based protocols. A new feature is the support for an optional SD card.

Product Features

- PROFINET-Device
- MODBUS TCP Client
- Numerous protocols supported such as: http, https, FTP, SNTP, SNMP, SMTP, SQL, MySQL, DCP, etc.
- Free engineering with PC Worx Express (IEC 61131-3)
- Program memory and mass storage (512 kB/512 kB)
- Modbus TCP server
- HTML 5
- Integrated web server for visualization with WebVisit/atvise®
- Complete INTERBUS master (4096 I/O points)
- SD card up to 2 GB as optional plug-in parameterization memory
- 2 x Ethernet interfaces (integrated switch)



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	360.0 g
Custom tariff number	85371091
Country of origin	Germany

Controller - ILC 171 ETH 2TX - 2700975

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	80 mm
Height	119.8 mm
Depth	71.5 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above mean sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above mean sea level)
Shock	25g, Criterion 1, according to IEC 60068-2-27
Vibration (operation)	5g

Control system

Programming tool	PC WORX / PC WORX EXPRESS
Diagnostics tool	DIAG+
Configuration tool	Config+ Version 1.01 or later

Mechanical design

Weight	295 g
Diagnostics display	No
Controller redundancy	No

Data interfaces

Interface	INTERBUS local bus (master)
Connection method	Inline data jumper
Transmission speed	500 kBaud / 2 MBaud (can be switched)
Interface	Parameterization/operation/diagnostics
Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2), Ethernet 10/100 (RJ45)
Transmission speed	max. 115,2 kBit/s
Interface	Ethernet 10Base-T/100Base-TX
Connection method	RJ45 socket
Transmission speed	10/100 MBit/s

Controller - ILC 171 ETH 2TX - 2700975

Technical data

PROFINET

Device function	PROFINET device
-----------------	-----------------

Power supply

Typical current consumption	210 mA
Max. current consumption	870 mA (370 mA communications power + 500 mA analog voltage supply)
Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC
Residual ripple	± 5 %
Power dissipation	max. 5 W

Fieldbus function

Amount of process data	max. 4096 Bit (INTERBUS)
	max. 32768 Bit (internal Modbus Client)
Number of supported devices	max. 128
Number of local bus devices that can be connected	max. 63 (observe current consumption)
Number of devices with parameter channel	max. 24
Number of supported branch terminals with remote bus branch	max. 3

Direct I/Os

Input name	Digital inputs
Number of inputs	8
Connection method	Inline potential distributor
Description of the input	EN 61131-2 type 1 NPN/PNP
Output name	Digital outputs
Number of outputs	4
Connection method	2, 3, 4-wire
Maximum output current per channel	500 mA
Without analog input	yes
Without analog output	yes
Without pulse direction output	yes
Without counter input	yes

IEC 61131 runtime system

Programming tool	PC WORX / PC WORX EXPRESS
Program memory	512 kByte (43 K instructions (IL))
Mass storage	512 kByte
Retentive mass storage	48 kByte (NVRAM)
Number of control tasks	8
Realtime clock	Yes

Controller - ILC 171 ETH 2TX - 2700975

Technical data

General data

Processor	Altera Nios II 64 MHz
Diagnostics display	No

Standards and Regulations

Shock	25g, Criterion 1, according to IEC 60068-2-27
Vibration (storage/transport)	5g
Vibration (operation)	5g

Classifications

eCl@ss

eCl@ss 4.0	27250203
eCl@ss 4.1	27240601
eCl@ss 5.0	27242215
eCl@ss 5.1	27242207
eCl@ss 6.0	27242207
eCl@ss 7.0	27242207
eCl@ss 8.0	27242207
eCl@ss 9.0	27242207

ETIM

ETIM 3.0	EC000236
ETIM 4.0	EC000236
ETIM 5.0	EC000236

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172018
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

UL Listed / cUL Listed / RINA / BSH / LR / BV / ABS / EAC / EAC / cULus Listed

Controller - ILC 171 ETH 2TX - 2700975

Approvals


Ex Approvals

ATEX / UL Listed / cUL Listed / cULus Listed

Approvals submitted

Approval details

UL Listed 

cUL Listed 

RINA

BSH

LR

BV

ABS

EAC

EAC

cULus Listed 