

## Router - FL MGUARD RS4000 TX/TX-P - 2702259

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Security device in metal housing, with ATEX and IECEx approval with extended temperature range, SD card slot, OPC inspector, VPN for up to 250 tunnels with additional license as an option, intelligent firewall with full scope of functions for maximum security and ease of configuration, router with NAT/1:1 NAT, optional CIFS Integrity Monitoring

The figure shows the standard item


### Product Description

Router with intelligent firewall and OPC inspector with ATEX and IECEx approval (VPN for up to 250 tunnels with additional license as an option), CIFS Integrity Monitoring (as an option), metal housing, slot for SD memory card, extended temperature range

### Why buy this product

- Maximum security
- OPC firewall
- Deep Packet Inspection
- OPC inspector
- Maximum performance
- Central management tool

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 064161
GTIN	4055626064161
Weight per Piece (excluding packing)	880.000 g
Custom tariff number	85176200
Country of origin	Germany

### Technical data

Note

# Router - FL MGUARD RS4000 TX/TX-P - 2702259

## Technical data

### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

### Dimensions

Width	45 mm
Height	130 mm
Depth	114 mm

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (5 % ... 95%, relative humidity 95%, temporary condensation according to 3K7/IEC EN 60721-3-3 (except for wind-driven precipitation and ice buildup))

### Interfaces

Interface 1	Ethernet
No. of ports	2 (RJ45 ports)
Connection method	RJ45
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
Interface 2	Signal contact
Connection method	Plug-in/screw connection via COMBICON
Interface 3	VPN - release button
Connection method	24 V DC/250 mA can be connected as an option

### Function

Basic functions	Router with intelligent firewall and OPC inspector with ATEX and IECEx approval (VPN for up to 250 tunnels with additional license as an option), CIFS Integrity Monitoring (as an option), metal housing, slot for SD memory card, extended temperature range, high-performance firewall/ VPN: up to 124 Mbps/40 Mbps
Supported browsers	HTTPS support required
Processor	330 MHz
Status and diagnostic indicators	LEDs:P1, P2, Fault, State, Error, LAN, WAN
Signal contact control voltage	24 V DC (typical)
Signal contact control current	250 mA (short-circuit resistant)

### Security functions

## Router - FL MGUARD RS4000 TX/TX-P - 2702259

### Technical data

#### Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 40 Mbps (Router mode, VPN bidirectional throughput)
	max. 27 Mbps (Stealth mode, VPN bidirectional throughput)
Number of VPN tunnels	0 (up to 250 tunnels with additional license as an option)
Encryption methods	DES, 3DES, AES-128, -192, -256
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1
1:1 Network Address Translation (NAT) in the VPN	Supported
Firewall data throughput	max. 124 Mbps (Router mode, default firewall rules, bidirectional throughput)
	max. 61 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall with full scope of functions, deep packet inspection for OPC classic
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	Standard routing, NAT, 1:1-NAT, port forwarding

#### Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

#### Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	9 V DC ... 36 V DC
Typical current consumption	100 mA (at U <sub>S</sub> = 24 V DC)
Max. current consumption	0.24 A

#### General

Mounting type	DIN rail
Type AX	Stand-alone
Net weight	660 g
Housing material	Metal

#### Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
---------------------------------	---------------

## Router - FL MGUARD RS4000 TX/TX-P - 2702259

### Technical data

#### Conformity with EMC directives

Test standard	IEC 61000-4-2 (ESD)
Test result	6 kV contact discharge, 8 kV air discharge
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	10 V/m (80 MHz ... 2000 MHz)
Test standard	IEC 61000-4-4 (burst)
Test result	2 kV power line, 1kV data line
Test standard	IEC 61000-4-5 (surge)
Test result	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)

#### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	6 kV contact discharge, 8 kV air discharge
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	10 V/m (80 MHz ... 2000 MHz)
Test standard	IEC 61000-4-4 (burst)
Test result	2 kV power line, 1kV data line
Test standard	IEC 61000-4-5 (surge)
Test result	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)
Noise emission	EN 55022 / Class B
Noise immunity	EN 61000-6-2:2005
Conformance	CE-compliant
ATEX	# II 3G Ex nA IIC T4 Gc
IECEX	Ex nA IIC T4 Gc

### Approvals

#### Approvals

---

Approvals

UL Listed / cUL Listed / cULus Listed

---



# Router - FL MGUARD RS4000 TX/TX-P - 2702259

## Approvals

Ex Approvals

IECEX / UL Listed / cUL Listed / ATEX / cULus Listed

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
cULus Listed	