

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Managed Switch 2000, 5 RJ45 ports 10/100 Mbps, Degree of protection IP20

Why buy this product

- ☑ Unmanaged Mode
- ✓ RSTP
- ✓ VLANs
- MRP client

Ethernet

Key Commercial Data

Packing unit	1
GTIN	4 055626 128344
GTIN	4055626128344
Custom tariff number	85176200

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	45 mm
Height	130 mm
Depth	115 mm



Technical data

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C 60 °C
Ambient temperature (storage/transport)	-40 °C 85 °C
Permissible humidity (operation)	10 % 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % 95 % (non-condensing)
Air pressure (operation)	86 kPa 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	86 kPa 108 kPa (1500 m above sea level)

Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	5 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Copper
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status

Function

Basic functions	Store-and-forward switch, complies with IEEE 802.3
Management	Web-based management (HTTP/HTTPS)
	SNMPv1/v2/v3
	Command-line interface (Telnet, SSH)
Diagnostic functions	RMON History
	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
	N:1-Portmirroring
	ACD (Address Conflict Detection)
Filter functions	Quality of Service (4 priority classes)
	Port-Priorisierung
	VLAN (up to 8 VLANs)
	IGMP Snooping (32 groups)
	IGMP Query
	Auto-Query-Port
	Extended Multicast Filtering
MAC address table	8k
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)



Technical data

Function

IP parameterization	DHCP-Client
	DHCP server (port based)
	BootP
PROFINET IO conformance class	Conformance-Class A
Status and diagnostic indicators	LEDs: US (power supply), 2 LEDs per Ethernet port (Link/Activity and Speed)

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

Supply voltage

Supply voltage	24 V DC (single)
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Supply voltage range	18.5 V DC 30.5 V DC
Typical current consumption	165 mA (at U _S = 24 V DC)
Current consumption	165 mA

General

Mounting type	DIN rail
Type AX	Book type
Net weight	365 g
Housing material	Polycarbonate fiber reinforced
MTTF	507.8 Years (SN 29500 standard, temperature 25 °C, operating cycle 21 % (5 days a week, 8 hours a day))
	246.55 Years (SN 29500 standard, temperature 40 °C, operating cycle 34.25 % (5 days a week, 12 hours a day))
	56.66 Years (SN 29500 standard, temperature 55 °C, operating cycle 100 % (7 days a week, 24 hours a day))

Connection data

Connection method	Screw connection
Conductor cross section solid min.	0.14 mm²
Conductor cross section solid max.	1.5 mm²
Conductor cross section flexible min.	0.14 mm²
Conductor cross section flexible max.	1.5 mm²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	16
Stripping length	9 mm

Standards and Regulations



Technical data

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	EN 61000-4-3 (electromagnetic fields)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion B
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2
Vibration (storage/transport)	2g, criterion 1 according to IEC 60068-2-6
Free from substances that could impair the application of coating	Yes
Vibration (operation)	2g, according to IEC 60068-2-6

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50	
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"	

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

Approval details

UL Listed



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

FILE E 238705



Approvals

cUL Listed	C UL	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
EAC	EAE		RU C- DE.A*30.B00767
cULus Listed	C UL US		

Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com