

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



D-SUB connector, 9-pos., male connector, cable entry  $< 35^{\circ}$ , bus system: PROFIBUS DP up to 12 Mbps with PG D-SUB socket for connecting a programming device, termination resistor can be switched on via slide switch, pin assignment: 3, 5, 6, 8; screw connection terminal blocks



### **Key Commercial Data**

Packing unit	1 pc
Weight per Piece (excluding packing)	58.2 g
Custom tariff number	85366990
Country of origin	Germany

#### Technical data

#### **Dimensions**

Max. cable diameter	8.4 mm
Min. cable diameter	7.6 mm
Width	16.6 mm
Height	39.4 mm
Length	58 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C 75 °C
Ambient temperature (storage/transport)	-25 °C 80 °C
Altitude	5000 m (For restrictions see manufacturer's declaration)

#### General

Nominal voltage U <sub>N</sub>	5 V
Nominal current I <sub>N</sub>	100 mA
Bus system	PROFIBUS DP
Signal	PROFIBUS
Insertion/withdrawal cycles	> 200



### Technical data

### General

SUBCON fixing screws	4-40 UNC			
Tightening torque	0.4 Nm			
Housing material	ABS, metal-plated			
Pin assignment	3, 5, 6, 8			
MTTF	6706 Years (SN 29500 standard, temperature 25°C, operating cycle 21 % (5 days a week, 8 hours a day))			
	1817 Years (SN 29500 standard, temperature 40 °C, operating cycle 34.25 % (5 days a week, 12 hours a day))			
	155 Years (SN 29500 standard, temperature 40°C, operating cycle 100 % (7 days a week, 24 hours a day))			

#### Connection data

Connection	D-SUB connection			
Number of positions	9			
Connection method	D-SUB connector			
Termination resistor	390 Ω			
	220 Ω			
	390 Ω (Can be connected externally)			
Connection	PCB connection			
Connection method	Screw connection			
Conductor cross section flexible min.	0.14 mm²			
Conductor cross section flexible max.	1 mm²			
Conductor cross section solid min.	0.14 mm²			
Conductor cross section solid max.	1.5 mm²			
Min. AWG conductor cross section, flexible	26			
Max. AWG conductor cross section, flexible	18			
Conductor cross section AWG min.	26			
Conductor cross section AWG max.	16			
Stripping length	5 mm			
Tightening torque	0.4 Nm			
Connection	Programming connection			
Number of positions	9			
Connection method	D-SUB socket			

## Standards and Regulations

Connection in acc. with standard	CUL
ATEX	# II 3 G Ex nA IIC T4 Gc X



### Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440302

#### **ETIM**

ETIM 2.0	EC001132
ETIM 3.0	EC001132
ETIM 4.0	EC001132
ETIM 5.0	EC001132

### **UNSPSC**

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

## Approvals

Δ	n	n	r	٦١.	/a	Ie
_	LJ	u	ı	JV	$^{\prime}$	1.7

Approvals

UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized

Ex Approvals


**ATEX** 

Approvals submitted

Approval details




## Approvals




### Drawings

### Schematic diagram




Stripping specifications

### Dimensional drawing










Right-hand side cable entry



Schematic diagram



Right-hand side cable entry

Phoenix Contact 2016 @ - all rights reserved http://www.phoenixcontact.com