

Feed-through terminal block - DK-BIC-35 - 2749880

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Feed-through terminal block for VAL and FLT applications

Product Features

- Biconnect feed-through terminal block
- For wiring mixed combinations of lightning and surge arresters
- As a system extension for FLASHTRAB and VALVETRAB applications



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 108212
Weight per Piece (excluding packing)	91.1 g
Custom tariff number	85363010
Country of origin	Germany

Technical data

Dimensions

Width	17.7 mm
Height	89.8 mm
Depth	65.5 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

General

Feed-through terminal block - DK-BIC-35 - 2749880

Technical data

General

Standards/specifications	IEC 60947-7-1 2002
	DIN EN 61643-11 2002
	IEC 61643-1 2005
Rated voltage	500 V AC/DC
Impulse discharge current (10/350)#µs, charge	50 As
Impulse discharge current (10/350)#µs, specific energy	2.5 MJ/Ω
Impulse discharge current (10/350)#µs, peak value I _{imp}	100 kA
Maximum continuous voltage U _c	500 V AC
	500 V DC
Standards for clearances and creepage distances	DIN VDE 0110-1
	IEC 60664-1
Mounting type	DIN rail: 35 mm
Color	jet black RAL 9005
Housing material	PA 6.6-FR
Overvoltage category	III
Degree of pollution	2
Flammability rating according to UL 94	V-0
Type	Rail-mountable module, one-piece
Connection method	Screw connection
Connection type IN	Biconnect screw terminal block
Connection type OUT	Biconnect screw terminal block
Screw thread	M5
Stripping length	14.5 mm
Conductor cross section flexible min.	0.5 mm ²
Conductor cross section flexible max.	25 mm ²
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	35 mm ²

Classifications

eCl@ss

eCl@ss 4.0	27140299
eCl@ss 4.1	27140299
eCl@ss 5.0	27140202
eCl@ss 5.1	27140202
eCl@ss 6.0	27141140
eCl@ss 7.0	27141140

Feed-through terminal block - DK-BIC-35 - 2749880

Classifications

eCl@ss

eCl@ss 8.0	27141120
eCl@ss 9.0	27141120

ETIM

ETIM 2.0	EC000489
ETIM 3.0	EC000489
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals

Approvals

UL Recognized / KEMA-KEUR / EAC

Ex Approvals


Approvals submitted

Approval details

UL Recognized	
mm ² /AWG/kcmil	20-2
Nominal current I _N	100 A
Nominal voltage U _N	600 V


Feed-through terminal block - DK-BIC-35 - 2749880

Approvals



Drawings

Dimensional drawing



Circuit diagram

