


Component connector - ST-1N4007 - 2802329

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component plug, with universal diode, to connect 2-pos. components into the basic terminal block, height: 19 mm, color: Gray

Key Commercial Data

| | |
|--------------------------------------|--|
| Packing unit | 1 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 017918 074418 |
| Weight per Piece (excluding packing) | 7.38 g |
| Custom tariff number | 85366990 |
| Country of origin | Poland |

Technical data

General

| | |
|--|------|
| Color | gray |
| Insulating material | PA |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|--------|-------|
| Width | 6 mm |
| Length | 42 mm |

Connection data

| | |
|-------------------|-----------------|
| Connection method | Plug connection |
|-------------------|-----------------|

Standards and Regulations

| | |
|--|-----|
| Connection in acc. with standard | CUL |
| Flammability rating according to UL 94 | V0 |

Component connector - ST-1N4007 - 2802329

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141145 |
| eCl@ss 5.1 | 27141145 |
| eCl@ss 6.0 | 27141149 |
| eCl@ss 7.0 | 27141149 |
| eCl@ss 8.0 | 27141149 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000897 |
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC002018 |
| ETIM 5.0 | EC002018 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11 | 39121409 |
| UNSPSC 12.01 | 39121409 |
| UNSPSC 13.2 | 39121409 |

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized


Ex Approvals


Approvals submitted

Approval details

Component connector - ST-1N4007 - 2802329

Approvals

| | |
|---|-------|
| UL Recognized  | |
| mm ² /AWG/kcmil | 30-14 |
| Nominal current I _N | 1 A |
| Nominal voltage U _N | 300 V |

| | |
|--|-------|
| cUL Recognized  | |
| mm ² /AWG/kcmil | 30-14 |
| Nominal current I _N | 1 A |
| Nominal voltage U _N | 300 V |

EAC

EAC

cULus Recognized 